



### Complex environment locking devices

#### Product description

3-pole, 4-wire grounding  
20A, 3Ø 250V/AC  
NEMA L15-20




L1520RW



L1620PY



L1620CY



L1620CW

**Dimensional information:**  
D-34-35

**Specification information:**  
Watertight industrial plugs & connectors: D-38  
Watertight industrial receptacles: D-39  
Severe duty industrial plugs & connectors: D-40  
Corrosion resistant: D-41

#### 3Ø plugs & connectors



Rating A	V/AC	NEMA	Description	Cord diameter	Color	Plug catalog no.	Connector catalog no.	
20	250	L15-20	3Ø watertight	0.36-0.84" (9.1-21.3mm)	Y	□ L1520PW	□ L1520CW	• •
			3Ø watertight	0.36-0.84" (9.1-21.3mm)	BK	□ L1520PWBK	□ L1520CWBK	• •
			3Ø severe duty	0.63-1.16" (15.9-29.4mm)	Y & BK	□ L1520PY	□ L1520CY	• •
			3Ø safety grip corrosion resistant	0.38-1.00" (9.7-25.4mm)	Y	□ CRL1520P	□ CRL1520C	• •

#### 3Ø receptacles




Rating A	V/AC	NEMA	Description	Color	Single receptacle catalog no.	
20	250	L15-20	Watertight	Y	□ L1520RW <sup>Δ*</sup>	• •
			Watertight	BK	□ L1520RWBK <sup>Δ*</sup>	• •
			Corrosion resistant	Y	□ CRL1520R <sup>†</sup>	

<sup>Δ</sup> cULus Listed, <sup>\*</sup> Not Fed Spec, <sup>†</sup> CSA certified


### Complex environment locking devices

#### Product description

3-pole, 4-wire grounding  
20A, 3Ø 480V/AC  
NEMA L16-20



L1620CY



L1620CW

#### 3Ø plugs & connectors



Rating A	V/AC	NEMA	Description	Cord diameter	Color	Plug catalog no.	Connector catalog no.	
20	480	L16-20	3Ø watertight	0.36-0.84" (9.1-21.3mm)	Y	□ L1620PW	□ L1620CW	• •
			3Ø watertight	0.36-0.84" (9.1-21.3mm)	BK	□ L1620PWBK	□ L1620CWBK	• •
			3Ø severe duty	0.63-1.16" (15.9-29.4mm)	Y & BK	□ L1620PY	□ L1620CY	• •
			3Ø safety grip corrosion resistant	0.38-1.00" (9.7-25.4mm)	Y	□ CRL1620P	□ CRL1620C	

#### 3Ø receptacles



Rating A	V/AC	NEMA	Description	Color	Single receptacle catalog no.	
20	480	L16-20	3Ø watertight	Y	□ L1620RW	• •
			3Ø watertight	BK	□ L1620RWBK	• •

#### Color information:

BK (Black), Y (Yellow)



(Black)

(Yellow)

**Compliances, specifications and availability are subject to change without notice.**



Indicates NAFTA compliant - Page Q-32

RoHS compliant - Page Q-32

### Complex environment locking devices

#### Product description

3-pole, 4-wire grounding  
20A, 3Ø 250V/AC  
NEMA L15-20




L1520RW



L1620PY



L1620CY



L1620CW

**Dimensional information:**  
D-34-35

**Specification information:**  
Watertight industrial plugs & connectors: D-38  
Watertight industrial receptacles: D-39  
Severe duty industrial plugs & connectors: D-40  
Corrosion resistant: D-41

#### 3Ø plugs & connectors



Rating	A	V/AC	NEMA	Description	Cord diameter	Color	Plug catalog no.	Connector catalog no.		
20	250	L15-20	3Ø watertight	0.36-0.84" (9.1-21.3mm)	Y	□ L1520PW	□ L1520CW	•	•	
			3Ø watertight	0.36-0.84" (9.1-21.3mm)	BK	□ L1520PWBK	□ L1520CWBK	•	•	
			3Ø severe duty	0.63-1.16" (15.9-29.4mm)	Y & BK	□ L1520PY	□ L1520CY	•	•	
			3Ø safety grip corrosion resistant	0.38-1.00" (9.7-25.4mm)	Y	□ CRL1520P	□ CRL1520C	•	•	

#### 3Ø receptacles




Rating	A	V/AC	NEMA	Description	Color	Single receptacle catalog no.		
20	250	L15-20	Watertight	Y	□ L1520RW <sup>Δ*</sup>	•	•	
			Watertight	BK	□ L1520RWBK <sup>Δ*</sup>	•	•	
			Corrosion resistant	Y	□ CRL1520R <sup>†</sup>			

<sup>Δ</sup> cULus Listed, <sup>\*</sup> Not Fed Spec, <sup>†</sup> CSA certified

### Complex environment locking devices

#### Product description

3-pole, 4-wire grounding  
20A, 3Ø 480V/AC  
NEMA L16-20



L1620CY

#### 3Ø plugs & connectors



Rating	A	V/AC	NEMA	Description	Cord diameter	Color	Plug catalog no.	Connector catalog no.		
20	480	L16-20	3Ø watertight	0.36-0.84" (9.1-21.3mm)	Y	□ L1620PW	□ L1620CW	•	•	
			3Ø watertight	0.36-0.84" (9.1-21.3mm)	BK	□ L1620PWBK	□ L1620CWBK	•	•	
			3Ø severe duty	0.63-1.16" (15.9-29.4mm)	Y & BK	□ L1620PY	□ L1620CY	•	•	
			3Ø safety grip corrosion resistant	0.38-1.00" (9.7-25.4mm)	Y	□ CRL1620P	□ CRL1620C			


#### 3Ø receptacles



Rating	A	V/AC	NEMA	Description	Color	Single receptacle catalog no.		
20	480	L16-20	3Ø watertight	Y	□ L1620RW	•	•	
			3Ø watertight	BK	□ L1620RWBK	•	•	

#### Color information:

BK (Black), Y (Yellow)



**Compliances, specifications and availability are subject to change without notice.**

Indicates NAFTA compliant - Page Q-32

RoHS compliant - Page Q-32