



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## L27HIDHEX39850D \*Delisted\* 27W Led Hid Repl 50K Hor Rot Base *Keystone Technologies*

Catalog Number	L27HIDHEX39850D
Manufacturer	Keystone Technologies
Description	Led Hid Replacement Lamp, 27W, EX39 Base, 5000K, 120-277V Input, Designed For Horizontal Application With Fold-Out Led Assemblies, Direct Drive
Weight per unit	1.9 (lbs/each)
Product Category	Led Specialty Lamps & Modules

### Features

Ballast Type	N/A
beam angle	180 Deg
Circuit Type	N/A
Input Voltage	120-277V
ip rating	IP64
lumens	4100
Nominal Length	N/A
Nominal Size	N/A
Number of Lamps	N/A
Output Current	N/A
Output Voltage	N/A
Sensor Type	N/A
Wattage	27
Wire Type	N/A

### Material, Color, and Finish

Base Type	EX39
color rendering index (cri)	>80 Deg
color temperature	5000
housing color	N/A

### Descriptions

Construction	N/A
Description	*DELISTED* 27W LED HID REPL 50K HOR ROT BASE
extra long description	Key KT-LED27HID-H-EX39-850-D-DP 27W
Long Description	LED HID REPLACEMENT LAMP, 27W, EX39 BASE, 5000K, 120-277V INPUT, DESIGNED FOR HORIZONTAL APPLICATION WITH FOLD-OUT LED ASSEMBLIES, DIRECT DRIVE
Product Type	27W, 4100 Lumen, 100-150W MH Equiv., IP64, Rot. Mogul Base



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Manufacturer Information

Brand	Keystone
GTIN	00890949016206
Manufacturers Part Number	KT-LED27HID-H-EX39-850-D-DP
UPC	890949016206

## Taxonomies, Classifications, and Categories

Category Description	LED SPECIALTY LAMPS & MODULES
----------------------	-------------------------------

## Packaging

Carton	1
Package	16
Weight Per each	1.93

## Uses, Certifications, and Standards

Energy Star	Y
-------------	---