



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



LAM2A600126Y 2BRL Alcu Lug Panduit Corporation

Catalog Number	LAM2A600126Y
Manufacturer	Panduit Corporation
Description	The LAM2A600-12-6Y Tin-Plated Aluminum Mechanical Lug, One-Hole, Two Barrel, Is Made From Extruded Aluminum Alloy to Provide Premium Electrical and Mechanical Performance For Wide Wire Range-Taking Capability That Helps Minimize Inventory Requirements. The Plated Steel or Aluminum Set Screw Provides A Durable Electrical Contract Between Conductor and Lug. UL Listed and Csa Certified For Use Up to 600 V and UL Temperature Rated 90 Degrees Celsius.
Weight per unit	3.1 (lbs/each)
Product Category	Large Terminals & Connectors

Features

amperage rating	NA
Material	Tin-Plated Aluminum
media	Yes
Number of Holes	1
Stud Size	1/2
Voltage Rating	600

Descriptions

Description	2BRL ALCU LUG
extra long description	PAN LAM2A600-12-6Y Pan-Lug™ LAM2A60
Long Description	The LAM2A600-12-6Y Tin-Plated Aluminum Mechanical Lug, one-hole, two barrel, is made from extruded aluminum alloy to provide premium electrical and mechanical performance for wide wire range-taking capability that helps minimize inventory requirements. The plated steel or aluminum set screw provides a durable electrical contract between conductor and Lug. UL Listed and CSA Certified for use up to 600 V and UL temperature rated 90 Degrees Celsius.
Product Type	Pan-Lug™ LAM2A600-12-6Y Mech Con-Lugs, 600, Tin PLT Al, STRT

Manufacturer Information

Brand	PANDUIT
GTIN	00074983592708
Manufacturers Part Number	LAM2A600-12-6Y
UPC	074983592708



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Taxonomies, Classifications, and Categories

Category Description	Comp & Mech Lugs and Butt Splices
Type	Mechanical Lug

Packaging

Carton	1
Package	6
Weight Per each	3.07

Uses, Certifications, and Standards

Application	Stranded Aluminum or Copper Code Conductor
Mounting standard	1.38 cULus Listed for use up to 600V & Temperature Rated to 90°C