



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



LBNEC10 4" Mogul Pulling Elbow

Crouse-Hinds

Catalog Number	LBNEC10
Manufacturer	Crouse-Hinds
Description	Eaton Crouse-Hinds Series Condulet Lbnec Mogul Pulling Elbow, Rigid/Imc, Copper-Free Aluminum, 4"
Weight per unit	22.3 (lbs/each)
Product Category	Alum

Features

connection	Tapered Threaded
dimensions	28.8400 IN X 5.5000 IN X 8.9400 IN

Material, Color, and Finish

Finish	Corrosion Resistant Metallic Painted
--------	--------------------------------------

Descriptions

Description	4" MOGUL PULLING ELBOW
extra long description	CRS-H LBNEC10 4 MOGUL PULLING ELBOW
Features	Crouse-Hinds series mogul bodies are installed in conduit systems to act as pull outlets for conductors that are stiff due to large size or type of insulation. Mogul bodies provide longer openings needed when pulling large conductors and prevent sharp bends and kinks during installation. Mogul conduit bodies are manufactured in trade sizes 1/2" to 6" and are available in Feraloy iron alloy and copper-free aluminum. Our iron alloy bodies are available with a hot dip galvanized finish for added corrosion
Long Description	Eaton Crouse-Hinds series Condulet LBNEC mogul pulling elbow, Rigid/IMC, Copper-free aluminum, 4"
Product Type	4 Mogul Pulling Elbow CVR Gask/Screws
Special Features	Maximum Wire Size 900 KCMIL, Dimension 28-27/32 In Length X 5-1/2 In Width X 8-15/16 In Height, Weight 2060 Lb per 100

Manufacturer Information

Brand	Eaton
GTIN	00782274519982
Manufacturers Part Number	LBNEC10
UPC	782274519982

Taxonomies, Classifications, and Categories

Category Description	Form 9 condulets, covers & gaskets
Type	Mogul pulling elbow



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Packaging

Carton	1
Weight Per each	22.25

Uses, Certifications, and Standards

Application	Ind Facilities & Factories - Industrial Facilities/Factories - OtherCommercial / Institutional Buildings / Structures - Commercial / Institutional Buildings / Structures - Other
standard	UL 514A, CSA C22.2