



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



LBNEC7 2-1/2" Al Lbnec MGL CNDT BC&G *Crouse-Hinds*

Catalog Number	LBNEC7
Manufacturer	Crouse-Hinds
Description	Eaton Crouse-Hinds Series Condulet Lbnec Mogul Pulling Elbow, Rigid/Imc, Copper-Free Aluminum, 2-1/2"
Weight per unit	N/A
Product Category	Alum

Features

connection	Tapered Threaded
dimensions	22.0000 IN X 4.5000 IN X 7.5300 IN

Material, Color, and Finish

Finish	Corrosion Resistant Metallic Painted
--------	--------------------------------------

Descriptions

Description	2-1/2" AL LBNEC MGL CNDT BC&G
extra long description	CRS-H LBNEC7 2 1/2 MOGUL PULLING EL
Features	Crouse-Hinds series mogul bodies are installed in conduit systems to act as pull outlets for conductors that are stiff due to large size or type of insulation. Mogul bodies provide longer openings needed when pulling large conductors and prevent sharp bends and kinks during installation. Mogul conduit bodies are manufactured in trade sizes 1/2" to 6" and are available in Feraloy iron alloy and copper-free aluminum. Our iron alloy bodies are available with a hot dip galvanized finish for added corrosion
Long Description	Eaton Crouse-Hinds series Condulet LBNEC mogul pulling elbow, Rigid/IMC, Copper-free aluminum, 2-1/2"
Product Type	2 1/2 Mogul Pulling Elbow CVR Gask/Screw
Special Features	Maximum Wire Size 500 KCMIL, Dimension 22 In Length X 4-1/2 In Width X 7-17/32 In Height, Weight 1003 Lb per 100

Manufacturer Information

Brand	Crouse-Hinds
GTIN	00782274519951
Manufacturers Part Number	LBNEC7
UPC	782274519951

Taxonomies, Classifications, and Categories

Type	Mogul pulling elbow
------	---------------------



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Packaging

Carton	1
Weight Per each	0

Uses, Certifications, and Standards

Application	Ind Facilities & Factories - Industrial Facilities/Factories - OtherCommercial / Institutional Buildings / Structures - Commercial / Institutional Buildings / Structures - Other
standard	UL 514A, CSA C22.2