



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## **LD18T848P840DVDI 18W Led T8 0-10V Dim 120-277V 2100LM** *Keystone Technologies*

Catalog Number	LD18T848P840DVDI
Manufacturer	Keystone Technologies
Description	18W Led T8 Tube, Plastic-Aluminum Construction, 120-277V Input, 4 4000K, Direct Drive, 0-10V Dimmable
Weight per unit	1.1 (lbs/each)
Product Category	Shape & Circular Lamps

### Features

Ballast Type	N/A
beam angle	180 Deg
Circuit Type	N/A
Input Voltage	120-277V
ip rating	N/A
lumens	2100
Nominal Length	48 in
Nominal Size	N/A
Number of Lamps	N/A
Output Current	N/A
Output Voltage	N/A
Sensor Type	N/A
Wattage	18
Wire Type	N/A

### Material, Color, and Finish

Base Type	G13
color rendering index (cri)	>80 Deg
color temperature	3500
housing color	N/A

### Descriptions

Construction	N/A
Description	18W LED T8 0-10V DIM 120-277V 2100LM
extra long description	Key KT-LED18T8-48P-840-D-VDIM-CP 18
Long Description	18W LED T8 TUBE, PLASTIC-ALUMINUM CONSTRUCTION, 120-277V INPUT, 4 4000K, DIRECT DRIVE, 0-10V DIMMABLE
Product Type	18W, 2100 Lumen, 4', 120' Beam Angle, Ballast Bypass, 0-10V



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Manufacturer Information

Brand	Keystone
GTIN	00890949017111
Manufacturers Part Number	KT-LED18T8-48P-840-D-VDIM-CP
UPC	890949017111

## Taxonomies, Classifications, and Categories

Category Description	LED LINEAR STRAIGHT(Fluor replacement), U-SHAPE & CIRCULAR LAMPS
----------------------	------------------------------------------------------------------

## Packaging

Carton	20
Weight Per each	1.05

## Uses, Certifications, and Standards

Energy Star	Y
-------------	---