



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



LD18.5T848GC850D 18.5W Led T8 48" 50K 120-277V *Keystone Technologies*

| | |
|------------------|---|
| Catalog Number | LD18.5T848GC850D |
| Manufacturer | Keystone Technologies |
| Description | Linear Fluorescent Led Lamp, Linear, Single/Double Ended, Instant Start Type; 47.15 Inch; UI (Canada and Us), UI, NSF/Ansi, Etl, DLC Approval; Food Equipment Application; 120 to 277 Volt Ac Voltage Rating; 1.1 Inch Diameter |
| Weight per unit | N/A |
| Product Category | 20170616143153 |

Features

| | |
|-------------------|--|
| Beam Spread Angle | 240 Degree |
| Current Rating | 0.15 Amp at 120 Volt AC, 0.07 Amp at 277 Volt AC |
| Glass Finish | FROSTED |
| Intensity | 2600 LUMEN |
| Item | LED Tube |
| Voltage Rating | 120 to 277 Volt AC |
| Wattage | 18.5 Watt |

Material, Color, and Finish

| | |
|-----------------------------|------------------|
| Base Type | G13 Medium 2-Pin |
| Color Rendering Index | 83 |
| Color Temperature in Kelvin | 5000 |

Dimensions and Weight

| | |
|----------|------------|
| Diameter | 1.1 Inch |
| Length | 47.15 Inch |

Descriptions

| | |
|------------------------|---|
| Additional Information | RoHS Compliant; Shatter Proof Coated Glass; Efficacy 141 Lumen per Watt; Visible Light Area 325 Degree; Temperature -4 to 113 Deg F |
| Commodity Description | Led Linear Fluorescent Straight, U-Shape & Circular Lamps |
| Description | 18.5W LED T8 48" 50K 120-277V |
| Long Description | LINEAR FLUORESCENT LED LAMP, LINEAR, SINGLE/DOUBLE ENDED, INSTANT START TYPE; 47.15 INCH; UL (CANADA AND US), UL, NSF/ANSI, ETL, DLC APPROVAL; FOOD EQUIPMENT APPLICATION; 120 TO 277 VOLT AC VOLTAGE RATING; 1.1 INCH DIAMETER |



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Manufacturer Information

| | |
|---------------------------|---------------------------|
| Brand | Keystone Technologies |
| Manufacturers Part Number | KT-LED18.5T8-48GC-850-DX2 |
| Model | 800 |

Taxonomies, Classifications, and Categories

| | |
|----------------------|--|
| Category Description | LED LINEAR STRAIGHT(Fluor replacement), U-SHAPE & CIRCULAR LAMPS |
| Type | Linear, Single/Double Ended, Instant Start |

Packaging

| | |
|-----------------|----|
| Carton | 1 |
| Package | 25 |
| Weight Per each | 0 |

Uses, Certifications, and Standards

| | |
|-------------|--|
| Application | Food Equipment |
| Approval | UL (Canada and US), UL, NSF/ANSI, ETL, DLC |