



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



LED12BR40DIMH084 12W Led BR40 40K 1100LM Dim *Sylvania-Ledvance*

| | |
|------------------|---|
| Catalog Number | LED12BR40DIMH084 |
| Manufacturer | Sylvania-Ledvance |
| Description | Led BR40, 12W, Dimmable, 80CRI, 1100 Lumen, 4000K, 25000 Life |
| Weight per unit | 1.4 (lbs/each) |
| Product Category | Lighting |

Features

| | |
|----------------|------------|
| average life | 25000 |
| Base | E26 Medium |
| Lamp Type | LED BR40 |
| lumens | 1,100 |
| Shape | BR40 |
| Voltage | 120.00 V |
| Voltage Rating | 120.00 |
| Wattage | 12.00 |

Material, Color, and Finish

| | |
|-----------------------------|----|
| color rendering index (cri) | 80 |
|-----------------------------|----|

Dimensions and Weight

| | |
|------|------|
| Size | 4.88 |
|------|------|

Descriptions

| | |
|------------------------|---|
| Description | 12W LED BR40 40K 1100LM DIM |
| extra long description | SYL LED12BR40DIMHO840G6RP/41110 LED |
| Long Description | LED BR40, 12W, Dimmable, 80CRI, 1100 Lumen, 4000K, 25000 life |
| Product Type | LED12BR40DIMHO840G6RP 6/CS 1/Sku |

Manufacturer Information

| | |
|---------------------------|-----------------------------|
| Brand | SYLVANIA |
| GTIN | 00046135411106 |
| Manufacturers Part Number | LED12BR40DIMHO840G6RP/41110 |
| UPC | 046135411106 |

Taxonomies, Classifications, and Categories

| | |
|----------------------|------------------------------------|
| Category Description | LED REFLECTOR GU, MR R SHAPE LAMPS |
|----------------------|------------------------------------|

Packaging

| | |
|-----------------|-------|
| Carton | 1 |
| Package | 6 |
| Weight Per each | 1.432 |



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Uses, Certifications, and Standards

standard

RoHS
