



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



LED14ET8G4850 14W Led T8 48" 50K Type A 2050LM 80cri

Ge By Current Lamps

| | |
|------------------|--|
| Catalog Number | LED14ET8G4850 |
| Manufacturer | Ge By Current Lamps |
| Description | Linear Fluorescent Led Lamp, Non-Dimmable, Integrated Type; 48 Inch; UL, DLC Approval; Damp Location Application; 14 Watt Wattage; Led Tube; G13 Base Type; 50000 Life In Hour; T8 Shape Designation; 2050 Lumen Intensity; 5000; 80 Color Rendering Index |
| Weight per unit | 0.5380 (lbs/each) |
| Product Category | Shape & Circular Lamps |

Features

| | |
|-----------|------------|
| Intensity | 2050 Lumen |
| Item | LED Tube |
| Wattage | 14 Watt |

Material, Color, and Finish

| | |
|-----------------------------|------|
| Base Type | G13 |
| Color Rendering Index | 80 A |
| Color Temperature in Kelvin | 5000 |

Dimensions and Weight

| | |
|--------|---------|
| Length | 48 INCH |
|--------|---------|

Descriptions

| | |
|------------------------|--|
| Additional Information | Ballast Type Instant Start or Program Start |
| Commodity Description | Led Linear Fluorescent Straight, U-Shape & Circular Lamps |
| Description | 14W LED T8 48" 50K TYPE A 2050LM 80CRI |
| extra long description | NON-DIMMABLE, INTEGRATED TYPE; 48 INCH; UL, DLC APPROVAL; DAMP LOCATION APPLICATION; 14 WATT WATTAGE; LED TUBE; G13 BASE TYPE; 50000 LIFE IN HOUR; T8 SHAPE DESIGNATION; 2050 LUMEN INTENSITY; 5000; 80 COLOR RENDERING INDEX; BALLAST TYPE INSTANT START OR PROGRAM START |
| Long Description | LINEAR FLUORESCENT LED LAMP, NON-DIMMABLE, INTEGRATED TYPE; 48 INCH; UL, DLC APPROVAL; DAMP LOCATION APPLICATION; 14 WATT WATTAGE; LED TUBE; G13 BASE TYPE; 50000 LIFE IN HOUR; T8 SHAPE DESIGNATION; 2050 LUMEN INTENSITY; 5000; 80 COLOR RENDERING INDEX |
| Product Type | Linear Fluorescent Led Lamp |



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Manufacturer Information

| | |
|---------------------------|-------------------------|
| Brand | GE LIGHTING, INC./LAMPS |
| GTIN | 10043168343005 |
| Manufacturers Part Number | LED14ET8G4850 |
| UPC | 043168343008 |

Taxonomies, Classifications, and Categories

| | |
|----------------------|--|
| Category Description | LED LINEAR STRAIGHT(Fluor replacement), U-SHAPE & CIRCULAR LAMPS |
| Type | Non-Dimmable, Integrated |

Packaging

| | |
|-----------------|-------|
| Carton | 1 |
| Package | 20 |
| Weight Per each | 0.538 |

Uses, Certifications, and Standards

| | |
|-------------|---------------|
| Application | Damp Location |
| Approval | UL, DLC |