



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



LED16.5PAR38HD27 16.5W Led PAR38 27K 1250LM *Sylvania-Ledvance*

| | |
|------------------|--|
| Catalog Number | LED16.5PAR38HD27 |
| Manufacturer | Sylvania-Ledvance |
| Description | OBSAR38HDDIM927G2NFL2 Led PAR38, 16.5W, Dimmable, 91CRI, 1250 Lumen, 2700K, 25000 Life |
| Weight per unit | 1.2 (lbs/each) |
| Product Category | Led Parabolic Reflector Par SH |

Features

| | |
|----------------|------------|
| average life | 25000 |
| Base | E26 Medium |
| Lamp Type | LED PAR38 |
| lumens | 1,250 |
| Shape | PAR38 |
| Voltage | 120.00 V |
| Voltage Rating | 120.00 |
| Wattage | 16.50 |

Material, Color, and Finish

| | |
|-----------------------------|-------------|
| color rendering index (cri) | 91 |
| Style | PAR38-shape |

Dimensions and Weight

| | |
|------|------|
| Size | 4.74 |
|------|------|

Descriptions

| | |
|------------------------|--|
| Description | 16.5W LED PAR38 27K 1250LM |
| extra long description | SYL LED16.5PAR38/HD/DIM/927/NFL25/7 |
| Long Description | OBSAR38HDDIM927G2NFL2 LED PAR38, 16.5W, Dimmable, 91CRI, 1250 Lumen, 2700K, 25000 life |
| Product Type | LED16.5PAR38HDDIM927NFL25 6/CS 1/Sku |

Manufacturer Information

| | |
|---------------------------|--------------------------------|
| Brand | SYLVANIA |
| GTIN | 00046135783531 |
| Manufacturers Part Number | LED16.5PAR38/HD/DIM/927/NFL25/ |
| UPC | 046135783531 |

Taxonomies, Classifications, and Categories

| | |
|----------------------|---------------------|
| Category Description | LED PAR SHAPE LAMPS |
|----------------------|---------------------|

Packaging

| | |
|-----------------|--------|
| Carton | 1 |
| Package | 6 |
| Weight Per each | 1.1566 |



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Uses, Certifications, and Standards

standard

RoHS