



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



LED23A21DIM0850U 23W Led A21 50K Dim 2550LM

Sylvania-Ledvance

| | |
|------------------|---|
| Catalog Number | LED23A21DIM0850U |
| Manufacturer | Sylvania-Ledvance |
| Description | Led A21, 23W, Dimmable, 80CRI, 2600 Lumen, 5000K, 15000 Life, E26 Medium Base, Frosted Finish |
| Weight per unit | 0.8317 (lbs/each) |
| Product Category | Led A-Line A Shape Lamps |

Features

| | |
|----------------|------------|
| average life | 15000 |
| Base | E26 Medium |
| Lamp Type | LED A21 |
| lumens | 2,600 |
| Shape | A21 |
| Voltage | 120.00 V |
| Voltage Rating | 120.00 |
| Wattage | 23.00 |

Material, Color, and Finish

| | |
|-----------------------------|---------|
| color rendering index (cri) | 80 |
| Style | A-shape |

Dimensions and Weight

| | |
|------|------|
| Size | 2.93 |
|------|------|

Descriptions

| | |
|------------------------|---|
| Description | 23W LED A21 50K DIM 2550LM |
| extra long description | SYL LED23A21DIMO850URP/79735 LED23A |
| Long Description | LED A21, 23W, Dimmable, 80CRI, 2600 Lumen, 5000K, 15000 Life, E26 Medium Base, FROSTED Finish |
| Product Type | LED23A21DIMO850URP 6/CS 1/Sku |

Manufacturer Information

| | |
|---------------------------|--------------------------|
| Brand | SYLVANIA |
| GTIN | 00046135797354 |
| Manufacturers Part Number | LED23A21DIMO850URP/79735 |
| UPC | 046135797354 |

Taxonomies, Classifications, and Categories

| | |
|----------------------|------------------------|
| Category Description | LED A-LINE SHAPE LAMPS |
|----------------------|------------------------|

Packaging

| | |
|-----------------|--------|
| Carton | 1 |
| Package | 6 |
| Weight Per each | 0.8317 |



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Uses, Certifications, and Standards

standard

RoHS
