



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## LED15ET8850V6P \*Delisted\* 15W Led T8 48" 50K Glass 1800LM 36000HR *Ge By Current Lamps*

Catalog Number	LED15ET8850V6P
Manufacturer	Ge By Current Lamps
Description	35911 Led Tube Light, 15 W, 120 V, 45.7 A, 1800 LM, 48 In., T8, 36000 H Average Life, Plug-In, Linear Fluorescent Fixture, 80+ Color Rendering Index (Cri), 5000 K Color Temperature
Weight per unit	0.8000 (lbs/each)
Product Category	Shape & Circular Lamps

### Features

amperage rating	45.7
average life	36000
Fixture Type	Linear Fluorescent Fixture
lumens	1800
Shape	T8
Voltage Rating	120
Wattage	15

### Material, Color, and Finish

color rendering index (cri)	80+
-----------------------------	-----

### Dimensions and Weight

Size	48
------	----

### Descriptions

Description	*DELISTED* 15W LED T8 48" 50K GLASS 1800LM 36000HR
extra long description	GEL LED15ET8/850-V6P 35911 LED Tube
Long Description	35911 LED Tube Light, 15 W, 120 V, 45.7 A, 1800 LM, 48 in., T8, 36000 H average life, Plug-In, Linear Fluorescent Fixture, 80+ color rendering index (cri), 5000 K color temperature
Product Type	35911 Led Tube Lamps
Special Features	Features: Each LED tube is outfitted with an internal GE driver, Easy disposal, Non-Hazardous Waste, No UV

### Manufacturer Information

Brand	GE Current
GTIN	00043168359115
Manufacturers Part Number	LED15ET8/850-V6P
UPC	043168359115

### Taxonomies, Classifications, and Categories

Category Description	LED LINEAR STRAIGHT(Fluor replacement), U-SHAPE & CIRCULAR LAMPS
Type	LED Tube Light



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Packaging

Carton	1
Package	6
Weight Per each	0.8

## Uses, Certifications, and Standards

Application	Damp Location
Mounting	Plug-in
standard	UL