




GE  
Lighting

**11332 - LED7DA19/827**

GE LED A19 40w Replacement



**GENERAL CHARACTERISTICS**

Lamp Type	Replacement Lamps - A-line
Bulb	A19
Base	Medium Screw (E26)
Additional Info	White, Omnidirectional
Bulb Shape	A-19
Color	White
Dimming Capability	Yes
Equivalent Wattage (NOM)	40.0 W
Lamp Type	A-19
Life in Years (NOM)	22.8
Rated Life (NOM)	25000.0 h

**PHOTOMETRIC CHARACTERISTICS**

Color Rendering Index (CRI) (NOM)	80.0
Color Temperature (NOM)	2700.0 K
Initial Lumens (NOM)	450.0
Nominal Initial Lumens per Watt (NOM)	64.3

**ELECTRICAL CHARACTERISTICS**

Estimated Energy Cost per Year (NOM)	0.84
Voltage (NOM)	120.0
Wattage (NOM)	7.0

**DIMENSIONS**

Maximum Overall Length (MOL) (NOM)	112.7 mm
------------------------------------	----------

**PRODUCT INFORMATION**


Product Code	11332
Description	LED7DA19/827
Standard Package	00-Case
Standard Package GTIN	10043168113325
Standard Package Quantity	6
Sales Unit	Unit
No Of Items Per Sales Unit	1
No Of Items Per Standard Package	6
UPC	043168113328



GE  
Lighting

**11332 - LED7DA19/827**

GE LED A19 40w Replacement



**GENERAL CHARACTERISTICS**

Lamp Type	Replacement Lamps - A-line
Bulb	A19
Base	Medium Screw (E26)
Additional Info	White, Omnidirectional
Bulb Shape	A-19
Color	White
Dimming Capability	Yes
Equivalent Wattage (NOM)	40.0 W
Lamp Type	A-19
Life in Years (NOM)	22.8
Rated Life (NOM)	25000.0 h

**PHOTOMETRIC CHARACTERISTICS**

Color Rendering Index (CRI) (NOM)	80.0
Color Temperature (NOM)	2700.0 K
Initial Lumens (NOM)	450.0
Nominal Initial Lumens per Watt (NOM)	64.3

**ELECTRICAL CHARACTERISTICS**

Estimated Energy Cost per Year (NOM)	0.84
Voltage (NOM)	120.0
Wattage (NOM)	7.0

**DIMENSIONS**

Maximum Overall Length (MOL) (NOM)	112.7 mm
------------------------------------	----------

**PRODUCT INFORMATION**

Product Code	11332
Description	LED7DA19/827
Standard Package	00-Case
Standard Package GTIN	10043168113325
Standard Package Quantity	6
Sales Unit	Unit
No Of Items Per Sales Unit	1
No Of Items Per Standard Package	6
UPC	043168113328