



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



LED7WBR20830DIMG 7W Led R20 30K 550LM

Eiko LTD

| | |
|------------------|---|
| Catalog Number | LED7WBR20830DIMG |
| Manufacturer | Eiko LTD |
| Description | Features: Led BR20 Reflector Flood 7W-550LM Dimmable 3000K 80+Cri 120VAC E26 |
| Weight per unit | 0.1480 (lbs/each) |
| Product Category | Lighting |

Features

| | |
|----------------|--------------------|
| average life | 25,000 |
| Base | Medium Screw (E26) |
| beam angle | 120° |
| lumens | 550 |
| Shape | BR20 |
| Voltage Rating | 120 |
| Wattage | 7 |

Material, Color, and Finish

| | |
|-----------------------------|------|
| Color | K |
| color rendering index (cri) | 80+ |
| color temperature | 3000 |

Dimensions and Weight

| | |
|------|----------------|
| Size | 2.5 DIA X 3.82 |
|------|----------------|

Descriptions

| | |
|------------------------|---|
| Description | 7W LED R20 30K 550LM |
| extra long description | EIKO LED7WBR20/830-DIM-G9 LED BR20 |
| Long Description | Features: LED BR20 REFLECTOR FLOOD 7W-550LM DIMMABLE 3000K 80+CRI 120VAC E26 |
| Product Type | Led BR20 Reflector Flood 7W-550LM Dimmab |

Manufacturer Information

| | |
|---------------------------|----------------------|
| Brand | Eiko |
| GTIN | 00031293107640 |
| Manufacturers Part Number | LED7WBR20/830-DIM-G9 |
| UPC | 031293107640 |

Taxonomies, Classifications, and Categories

| | |
|----------------------|------------------------------------|
| Category Description | LED REFLECTOR GU, MR R SHAPE LAMPS |
|----------------------|------------------------------------|

Packaging

| | |
|-----------------|-------|
| Carton | 1 |
| Weight Per each | 0.148 |



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Uses, Certifications, and Standards

standard

cULus, Energy Star, RoHS
