



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



LED8WA190MN840B 8W Led A19 40K Non Dim 800LM - Oc 11072

Eiko LTD

| | |
|------------------|---|
| Catalog Number | LED8WA190MN840B |
| Manufacturer | Eiko LTD |
| Description | Features: 4000K Led A19 8W-800LM Enclosed 80+Cri 4000K E26 120 Vac |
| Weight per unit | 1.0 (lbs/each) |
| Product Category | Lighting |

Features

| | |
|----------------|--------------------|
| average life | 25,000 |
| Base | Medium Screw (E26) |
| beam angle | 240° |
| lumens | 800 |
| Shape | A19 |
| Voltage Rating | 120 |
| Wattage | 8 |

Material, Color, and Finish

| | |
|-----------------------------|------|
| Color | K |
| color rendering index (cri) | 80+ |
| color temperature | 4000 |

Dimensions and Weight

| | |
|------|-----------------|
| Size | 2.36 DIA X 4.25 |
|------|-----------------|

Descriptions

| | |
|------------------------|---|
| Description | 8W LED A19 40K NON DIM 800LM - OC 11072 |
| extra long description | EIKO LED8WA19/OMN/840-B 4000K LED A |
| Long Description | Features: 4000K LED A19 8W-800LM ENCLOSED 80+CRI 4000K E26 120 VAC |
| Product Type | 4000K Led A19 8W-800LM Enclosed 80+Cri 4 |

Manufacturer Information

| | |
|---------------------------|--------------------|
| Brand | Eiko |
| GTIN | 00031293110725 |
| Manufacturers Part Number | LED8WA19/OMN/840-B |
| UPC | 031293110725 |

Taxonomies, Classifications, and Categories

| | |
|----------------------|------------------------|
| Category Description | LED A-LINE SHAPE LAMPS |
|----------------------|------------------------|

Packaging

| | |
|-----------------|----|
| Carton | 1 |
| Package | 24 |
| Weight Per each | 1 |



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Uses, Certifications, and Standards

standard

cULus, Energy Star, RoHS
