



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

10917 Mill Creek Rd
66219-0000, KS Lenexa
Phone: 913-563-7000
Fax: 913-563-7050



LPJ110SP 110A 600V Class J Low Pea *Bussmann Fuses*

Catalog Number	LPJ110SP
Manufacturer	Bussmann Fuses
Description	Eaton Bussmann Series LPJ Fuse, Bussmann Series Class J Fuse, LPJ, Time-Delay, Dual-Element Current Limiting Fuse, 110 A, Non-Idicating Fuse, Interrupting Rating Of 300 Ka At 600 Vac and 100 Ka At 300 VDC
Weight per unit	0.8000 (lbs/each)
Product Category	Dual Element

Features

dimensions	5.7500 IN X 1.5000 IN X 1.5000 IN
media	Yes

Descriptions

Description	110A 600V CLASS J LOW PEA
extra long description	BUSS LPJ-110SP BUSSMAN FUSE (55
Features	Bussmann's UL Class J fuse products extend both our Low-Peak family of products with our LPJ_SP and LPJ_SPI dual-element, time-delay fuses as well as our Limitron line offering fast-acting JKS fuses. The LPJ fuses provide industry leading 300,000 amp interrupting rating at 600Vac RMS Sym and 100kA Vdc while delivering a minimum of 10 seconds of 500 percent rated current ride-through performance which is ideal for sizing of high inrush loads. The LPJ products are available with optional permanent replace fu
Long Description	Eaton Bussmann series LPJ fuse, Bussmann Series Class J fuse, LPJ, time-delay, dual-element current limiting fuse, 110 A, non-idicating fuse, interrupting rating of 300 kA at 600 Vac and 100 kA at 300 Vdc
Product Type	Bussman Fuse (55

Manufacturer Information

Brand	Eaton
GTIN	00051712523417
Manufacturers Part Number	LPJ-110SP
UPC	051712523417

Taxonomies, Classifications, and Categories

Category Description	Fuses & Fuse Accessories
Type	FUSE



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

10917 Mill Creek Rd
66219-0000, KS Lenexa
Phone: 913-563-7000
Fax: 913-563-7050

Packaging

Carton	1
Weight Per each	0.8

Uses, Certifications, and Standards

Application	Ind Facilities & Factories - Facility: Safety and Security Systems
standard	UL Listed ,CSA Certified,RoHS Compliant