



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## LR25 3/4" Alu LR SR5 Conduit Body

*Crouse-Hinds*

Catalog Number	LR25
Manufacturer	Crouse-Hinds
Description	Conduit Outlet Body, Epoxy Powder Painted (Body);Natural (Gasket), 3/4 In Trade Size, Threaded/Set Screw Connection, 7.3 Cu.In Capacity, 90 ° Angle, 3/4 In Hub Size, 5.07 In Length, 2.28 In Width, 10-1/8 In Height, 0.33 LB/Ea
Weight per unit	0.3300 (lbs/each)
Product Category	Alum

### Features

connection	Threaded / Set Screw
dimensions	5.0700 IN X 1.6400 IN X 2.2800 IN
Form	Series 5

### Material, Color, and Finish

Color	Gray
-------	------

### Dimensions and Weight

Length	5.07
--------	------

### Descriptions

Description	3/4" ALU LR SR5 CONDUIT BODY
extra long description	MIDWEST LR25 3/4 RGD LR COND BODY A
Features	Eaton's Crouse-Hinds Division Series 5 die cast copper-free aluminum conduit bodies, covers and gaskets are available for use with rigid or EMT conduit (with set screw). Conduit bodies are available in trade sizes 1/2" to 4", in the most popular conduit body shapes (C, LB, LL, LR, T) and 1/2" to 2" in TB and X shapes. The Series 5 family is available as components or pre-packaged in various configurations as a SnapPack assembly. In addition, Series 5 is completely interchangeable with other manufacturer

### Manufacturer Information

Brand	Eaton
GTIN	00784564140128
UPC	784564140128

### Taxonomies, Classifications, and Categories

Category Description	FORM 5 CONDULETS, COVERS, & GASKETS
Type	Conduit outlet body



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Packaging

Carton	10
Weight Per each	0.33

## Uses, Certifications, and Standards

Application	Commercial / Institutional Buildings / Structures - Commercial / Institutional Buildings / Structures - Other
Enclosure	Condulet
Mounting standard	Conduit UL, cUL