

Eaton LR777

Catalog Number: LR777

Eaton Crouse-Hinds series Condulet Form 7 conduit outlet body, Feraloy iron alloy, LR shape, 2-1/2"

Photo is representative

General specifications

Product Name	Catalog Number
Eaton Crouse-Hinds series Condulet Form 7 conduit outlet body	LR777
	UPC
	782274530406
Product Length/Depth	Product Height
10.5 in	5.75 in
Product Width	Product Weight
3.63 in	8 lb



Certifications and compliances

Area classification

Ordinary/Non-Hazardous Locations

Standards type

NEC/CEC

NEMA Rating

12

Product specifications

Shape

LR

Trade size

2-1/2"

Material

Feraloy iron alloy

Resources

Catalogs

[Crouse-Hinds series Form 7 catalog page](#)

Certification reports

[Condulet Form 7 Conduit Outlet Bodies and Covers UL certification](#)

[Condulet Form 7 Conduit Outlet Bodies and Covers Canadian certification](#)

Installation instructions

[IF 863 - Conduit Body Wire Pulling](#)

[IF 964 - Conduit Body Wire Pulling](#)

Specifications and datasheets

[Eaton Specification Sheet - LR777](#)

[Condulet Form 7 Industrial Grade Conduit Bodies](#)

Technical service bulletins

[Industrial Fittings Wire Fill Chart](#)

[Industrial Fittings Bend Radius and Cubic Capacity Chart](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)

Eaton LR777

Catalog Number: LR777

Eaton Crouse-Hinds series Condulet Form 7 conduit outlet body, Feraloy iron alloy, LR shape, 2-1/2"

Photo is representative

General specifications

Product Name	Catalog Number
Eaton Crouse-Hinds series Condulet Form 7 conduit outlet body	LR777
	UPC
	782274530406
Product Length/Depth	Product Height
10.5 in	5.75 in
Product Width	Product Weight
3.63 in	8 lb



Certifications and compliances

Area classification

Ordinary/Non-Hazardous Locations

Standards type

NEC/CEC

NEMA Rating

12

Product specifications

Shape

LR

Trade size

2-1/2"

Material

Feraloy iron alloy

Resources

Catalogs

[Crouse-Hinds series Form 7 catalog page](#)

Certification reports

[Condulet Form 7 Conduit Outlet Bodies and Covers UL certification](#)

[Condulet Form 7 Conduit Outlet Bodies and Covers Canadian certification](#)

Installation instructions

[IF 863 - Conduit Body Wire Pulling](#)

[IF 964 - Conduit Body Wire Pulling](#)

Specifications and datasheets

[Eaton Specification Sheet - LR777](#)

[Condulet Form 7 Industrial Grade Conduit Bodies](#)

Technical service bulletins

[Industrial Fittings Wire Fill Chart](#)

[Industrial Fittings Bend Radius and Cubic Capacity Chart](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)