

Specifications

Eaton LR87

Eaton Crouse-Hinds series Condulet Form 7 conduit outlet body, Feraloy iron alloy, LR shape, 3"



Photo is representative



General specifications

PRODUCT NAME	Eaton Crouse-Hinds series Condulet Form 7 conduit outlet body
CATALOG NUMBER	LR87
UPC	782274529707
PRODUCT LENGTH/DEPTH	10.5 in
PRODUCT HEIGHT	5.75 in
PRODUCT WIDTH	4.38 in
PRODUCT WEIGHT	10.7 lb



Powering Business Worldwide

Certifications and compliances

AREA CLASSIFICATION	Ordinary/Non-Hazardous Locations
STANDARDS TYPE	NEC/CEC
NEMA RATING	12

Product specifications

SHAPE	LR
TRADE SIZE	3"
MATERIAL	Feraloy iron alloy

Resources

CATALOGS	Crouse-Hinds series Form 7 catalog page
CERTIFICATION REPORTS	Condulet Form 7 Conduit Outlet Bodies and Covers UL certification Condulet Form 7 Conduit Outlet Bodies and Covers Canadian certification
INSTALLATION INSTRUCTIONS	IF 964 - Conduit Body Wire Pulling IF 863 - Conduit Body Wire Pulling
SPECIFICATIONS AND DATASHEETS	Eaton Specification Sheet - LR87 Condulet Form 7 Industrial Grade Conduit Bodies
TECHNICAL SERVICE BULLETINS	Industrial Fittings Wire Fill Chart Industrial Fittings Bend Radius and Cubic Capacity Chart

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

Follow us on social media to get the latest product and support information.

All other trademarks are property of their respective owners.



Specifications

Eaton LR87

Eaton Crouse-Hinds series Condulet Form 7 conduit outlet body, Feraloy iron alloy, LR shape, 3"



Photo is representative



General specifications

PRODUCT NAME	Eaton Crouse-Hinds series Condulet Form 7 conduit outlet body
CATALOG NUMBER	LR87
UPC	782274529707
PRODUCT LENGTH/DEPTH	10.5 in
PRODUCT HEIGHT	5.75 in
PRODUCT WIDTH	4.38 in
PRODUCT WEIGHT	10.7 lb



Powering Business Worldwide

Certifications and compliances

AREA CLASSIFICATION	Ordinary/Non-Hazardous Locations
STANDARDS TYPE	NEC/CEC
NEMA RATING	12

Product specifications

SHAPE	LR
TRADE SIZE	3"
MATERIAL	Feraloy iron alloy

Resources

CATALOGS	Crouse-Hinds series Form 7 catalog page
CERTIFICATION REPORTS	Condulet Form 7 Conduit Outlet Bodies and Covers UL certification Condulet Form 7 Conduit Outlet Bodies and Covers Canadian certification
INSTALLATION INSTRUCTIONS	IF 964 - Conduit Body Wire Pulling IF 863 - Conduit Body Wire Pulling
SPECIFICATIONS AND DATASHEETS	Eaton Specification Sheet - LR87 Condulet Form 7 Industrial Grade Conduit Bodies
TECHNICAL SERVICE BULLETINS	Industrial Fittings Wire Fill Chart Industrial Fittings Bend Radius and Cubic Capacity Chart

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

Follow us on social media to get the latest product and support information.

All other trademarks are property of their respective owners.

