



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



M22DDLGR Non-FLSH III DBL PB SIL-BZL GRN Top Red BTM

Eaton Corp

Catalog Number	M22DDLGR
Manufacturer	Eaton Corp
Description	Eaton M22 Modular Pushbutton, 22.5 MM, Extended- Dual Button Actuator, Momentary, Illuminated, Bezel: Silver, Button: Top Green, Bottom Red, IP66, Nema 4X, 13, Light 100, 000 Hours, Button 200, 000 Operations
Weight per unit	0.0500 (lbs/each)
Product Category	Push Button Complete Assemblie

Features

actuator	Extended, Dual button
operating cycles	Light: 100,000, button: 200,000

Dimensions and Weight

Depth	2.15
Height	0.52
Size	22.5 mm
Width	1.17

Descriptions

Description	NON-FLSH ILL DBL PB SIL-BZL GRN TOP RED BTM
extra long description	ETN M22-DDL-GR IP66, NEMA 4X, 13, L
Features	This attractive, functional line of pushbuttons features a space-saving construction that enables fast assembly. The complete illuminated M22 line offers LED light units to ensure high-quality brightness and up to 100,000 hours of illumination. Because of the rugged design of these pushbuttons, most operators and contact blocks exceed five million mechanical operations.
Long Description	Eaton M22 modular pushbutton, 22.5 mm, Extended- dual button actuator, Momentary, Illuminated, Bezel: Silver, Button: Top Green, Bottom Red, IP66, NEMA 4X, 13, Light 100,000 hours, Button 200,000 Operations
Product Type	IP66, Nema 4X, 13, Light 100, 000 Hours
Special Features	M22 series

Manufacturer Information

Brand	EATON CUTLER-HAMMER
GTIN	00786685272252
Manufacturers Part Number	M22-DDL-GR
Model	Modular pushbutton
UPC	786685272252



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Taxonomies, Classifications, and Categories

Category Description MINATURE PILOT DEVICES.22MM

Packaging

Carton 1

Weight Per each 0.05

Uses, Certifications, and Standards

Application Elec Assemblies, Panels & OEM - Electrical Assemblies, Panels
and OEMs

environmental conditions IP66, NEMA 4X, NEMA 13

standard CSA Certified,Lloyd's Register Certified,CCC Marked,CE
Marked,Bureau Veritas,GoST-R