



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



M22DRLW III MTN PB SiI-BZL FLSH WHT

Eaton Corp

Catalog Number	M22DRLW
Manufacturer	Eaton Corp
Description	Eaton M22 Modular Pushbutton, 22.5 MM, Flush, Maintained, Illuminated, Bezel: Silver, Button: White, IP67, IP69K, Nema 4X, 13, 1, 000, 000 Mechanical Operations
Weight per unit	0.9950 (lbs/each)
Product Category	Push Button Complete Assemblie

Features

actuator	Flush, Button
operating cycles	1 million

Dimensions and Weight

Depth	1.17
Height	0.39
Size	22.5 mm
Width	1.17

Descriptions

Description	ILL MTN PB SIL-BZL FLSH WHT
extra long description	ETN M22-DRL-W ILL MTN PB SIL-BZL FL
Features	This attractive, functional line of pushbuttons features a space-saving construction that enables fast assembly. The complete illuminated M22 line offers LED light units to ensure high-quality brightness and up to 100,000 hours of illumination. Because of the rugged design of these pushbuttons, most operators and contact blocks exceed five million mechanical operations.
Long Description	Eaton M22 modular pushbutton, 22.5 mm, Flush, Maintained, Illuminated, Bezel: Silver, Button: White, IP67, IP69K, NEMA 4x, 13, 1,000,000 mechanical operations
Product Type	III MTN PB SiI-BZL FLSH WHT
Special Features	M22 series

Manufacturer Information

Brand	Eaton
GTIN	00786685274645
Manufacturers Part Number	M22-DRL-W
Model	Modular pushbutton
UPC	786685274645

Taxonomies, Classifications, and Categories

Category Description	MINATURE PILOT DEVICES.22MM
----------------------	-----------------------------



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Packaging

Carton	1
Weight Per each	0.995

Uses, Certifications, and Standards

Application	Elec Assemblies, Panels & OEM - Electrical Assemblies, Panels and OEMs
environmental conditions	IP67, IP69K, NEMA 4X, NEMA 13
standard	Lloyd's Register Certified, CSA Certified, CCC Marked, CE Marked, Bureau Veritas, GoST-R