



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## M22MDRPRK01 MTN Mushroom PB Red 1NC Metal-BZL

Eaton Corp

Catalog Number	M22MDRPRK01
Manufacturer	Eaton Corp
Description	Eaton M22 Modular Pushbutton, Red, Modular Pushbutton, 1NC, Nema 4X, 13, IP67, IP69K (IP66 Key-Release), M22, 22.5 MM, Metal
Weight per unit	0.0700 (lbs/each)
Product Category	Push Button Complete Assemblie

### Features

action	Red
actuator	Mushroom
Contact Configuration	1 NC
dimensions	1.5000 IN X 1.5000 IN X 1.5000 IN

### Dimensions and Weight

Depth	1.5000
Height	1.5000
Size	22.5 mm
Width	1.5000

### Descriptions

Description	MTN MUSHROOM PB RED 1NC METAL-BZL
extra long description	ETN M22M-DRP-R-K01 MTN MUSHROOM PB
Features	This attractive, functional line of pushbuttons features a space-saving construction that enables fast assembly. The complete illuminated M22 line offers LED light units to ensure high-quality brightness and up to 100,000 hours of illumination. Because of the rugged design of these pushbuttons, most operators and contact blocks exceed five million mechanical operations.
Long Description	Eaton M22 modular pushbutton, Red, Modular Pushbutton, 1NC, NEMA 4x, 13, IP67, IP69K (IP66 key-release), M22, 22.5 mm, Metal
Product Type	MTN Mushroom PB Red 1NC, Metal-BZL

### Manufacturer Information

Brand	Eaton
GTIN	00786685862200
Manufacturers Part Number	M22M-DRP-R-K01
Model	Modular pushbutton
UPC	786685862200



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Taxonomies, Classifications, and Categories

Category Description	MINATURE PILOT DEVICES.22MM
Type	Modular pushbutton

## Packaging

Carton	1
Weight Per each	0.07

## Uses, Certifications, and Standards

Application	Stationary Machinery and Equipment Outside Factory - Stationary Machinery and Equipment Outside Factory - Other
environmental conditions	IP67, IP69K
standard	CSA Certified,CCC Marked,Lloyd&apos;s Register Certified,Bureau Veritas,GoST-R,CE Marked