



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## MBG075 3/4" Intersystem Bonding

*Bridgeport Fittings*

Catalog Number	MBG075
Manufacturer	Bridgeport Fittings
Description	3/4" Mighty-Bond® Intersystem Bonding Bridge and Coupling Combination
Weight per unit	0.3400 (lbs/each)
Product Category	Grounding & Bonding Equipment

### Features

Conductor Size	MCC-075: Copper Conductor Ranges: Solid #4 to #2 Bare AWG, Stranded #4 AWG - 3/0. Aluminum Conductor Range: Stranded #2 AWG to 3/0 AWG. IGB-075: Copper Conductor Ranges and Torques: #14 - #10 Sol/Str Torque 10 in-lbs, #8 - #6 Sol/Str Torque 45 in-lbs, #4 Str Torque 45 in-lbs, #4 Solid Torque 60 in-lbs
media	Yes

### Material, Color, and Finish

Conductor Material	Brass/Stainless Steel/Steel
--------------------	-----------------------------

### Dimensions and Weight

Size	3/4
------	-----

### Descriptions

Description	3/4" INTERSYSTEM BONDING
extra long description	BPT MBG-075 3/4" INTERSYSTEM BONDING
Long Description	3/4" Mighty-Bond® Intersystem Bonding Bridge and Coupling combination
Product Type	3/4" Intersystem Bonding
Special Features	Minimum enclosure plate thickness 14 Gauge (0.074 inches)

### Manufacturer Information

Brand	Bridgeport Fittings
GTIN	00781747023759
Manufacturers Part Number	MBG-075
UPC	781747023759

### Taxonomies, Classifications, and Categories

Category Description	SERVICE ENTRANCE FITTINGS: Weatherheads & Grounding Fittings & Ground Rods
Type	Intersystem Bonding Bridge



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Packaging

Carton	1
Package	5
Weight Per each	0.34

## Uses, Certifications, and Standards

Application	Used to bond one continuous length of grounding conductor to an enclosure thru a 3/4" trade size knockout, inside or outside of an enclosure or panel board and provides 3-equipment bonding terminations. Meets the requirement for Intersystem Bonding.
Patented	
standard	UL