



Powering Business Worldwide

[pe.eaton.com](http://pe.eaton.com)

## Eaton residential meter breaker

**MBT48B125BTS**

**UPC:**782116157365

**Dimensions:**

- **Height:** 25.5 IN
- **Length:** 4.94 IN
- **Width:** 14.44 IN

**Weight:**36.5 LB

**Warranties:**

- 10 year

**Specifications:**

- **Type:** All-in-ones
- **Amperage Rating:** 125A
- **Box Size:** C
- **Bus Material:** Aluminum
- **Enclosure:** NEMA 3R
- **Feed Type:** Top/bottom
- **Ground:** #6-300 kcmil
- **Interrupt Rating:** 22 kAIC
- **Main Circuit Breaker:** CSR2150
- **Mounting:** Surface mounting
- **Number Of Circuits:** 8
- **Number Of Jaws:** Four-jaw
- **Number Of Sockets:** 1
- **Number Of Spaces:** 4
- **Phase:** Single-phase
- **Security:** Ringless
- **Voltage Rating:** 120/240V

**Supporting documents:**

- [Dimensional Drawing - METER BREAKER TRAILER PANEL](#)
- [Eatons Volume 1-Residential and Light Commercial](#)
- [Eaton Specification Sheet - MBT48B125BTS](#)



**Certifications:**

- UL Listed

**Product compliance:**

- EUSERC Approved

---

© 2016 Eaton. All rights reserved.



Powering Business Worldwide

[pe.eaton.com](http://pe.eaton.com)

## Eaton residential meter breaker

**MBT48B125BTS**

**UPC:**782116157365

**Dimensions:**

- **Height:** 25.5 IN
- **Length:** 4.94 IN
- **Width:** 14.44 IN

**Weight:**36.5 LB

**Warranties:**

- 10 year

**Specifications:**

- **Type:** All-in-ones
- **Amperage Rating:** 125A
- **Box Size:** C
- **Bus Material:** Aluminum
- **Enclosure:** NEMA 3R
- **Feed Type:** Top/bottom
- **Ground:** #6-300 kcmil
- **Interrupt Rating:** 22 kAIC
- **Main Circuit Breaker:** CSR2150
- **Mounting:** Surface mounting
- **Number Of Circuits:** 8
- **Number Of Jaws:** Four-jaw
- **Number Of Sockets:** 1
- **Number Of Spaces:** 4
- **Phase:** Single-phase
- **Security:** Ringless
- **Voltage Rating:** 120/240V

**Supporting documents:**

- [Dimensional Drawing - METER BREAKER TRAILER PANEL](#)
- [Eatons Volume 1-Residential and Light Commercial](#)
- [Eaton Specification Sheet - MBT48B125BTS](#)



**Certifications:**

- UL Listed

**Product compliance:**

- EUSERC Approved

---

© 2016 Eaton. All rights reserved.