



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



MDL34R 3/4A Buss Small Dimension Fuse Slow Blow

Bussmann Fuses

Catalog Number	MDL34R
Manufacturer	Bussmann Fuses
Description	Eaton MDL Series Time-Delay Fuse 0.75A, 250 Vac, 32 VDC (Self Certified)
Weight per unit	0.0070 (lbs/each)
Product Category	Small Dimension Fuses

Features

amperage rating	0.75A
connection	Ferrule End X Ferrule End
dimensions	1.2500 IN X 0.2500 IN X 0.2500 IN
interrupt rating	35 AIC at 250 Vac 10 kAIC at 125 Vac
Material	Glass tube Nickel-plated brass end cap construction
Response Time	60 min at 135%, 120 sec at 200%, 5 sec at 200%
Voltage Rating	250 Vac, 32 Vdc (self certified)

Dimensions and Weight

Size	1/4 In Diameter X 1-1/4 In Length
------	-----------------------------------

Descriptions

Description	3/4A BUSS SMALL DIMENSION FUSE SLOW BLOW
extra long description	EFSE MDL-3/4-R BUSS SMALL DIMENSION
Features	Eaton's Bussmann Division develops and manufactures critical circuit protection, power management and electrical safety products designed to provide innovative circuit and power electronics protection, serving the commercial, data center, electrical vehicle, food and beverage, and other markets.
Long Description	Eaton MDL Series Time-delay fuse 0.75A, 250 Vac, 32 Vdc (self certified)
Product Type	Buss Small Dimension Fuse Slow Blow
Special Features	Interrupt Rating 35 Amp at 250 Vac, 10000 Amp at 125 Vac, Material Glass Tube, Nickel Plated Brass Endcap, ROHS Compliant

Manufacturer Information

Brand	Eaton
GTIN	00051712652261
Manufacturers Part Number	MDL-3/4-R
UPC	051712652261

Taxonomies, Classifications, and Categories

Category Description	GLASS FUSES (and ceramic)
Type	Time-delay fuse



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Packaging

Carton	1
Package	5
Weight Per each	0.007

Uses, Certifications, and Standards

Application	Ind Facilities & Factories - Facility: Safety and Security Systems
standard	RoHS Compliant,CE Marked