ELLIOTT ELECTRIC SUPPLY
We Deliver...Lower Cost, Quality Products, & Personal Service
805 South Timberlane Drive
El Dorado, AR 71730-0000
Phone: 8706396289
Fax: 8708648850



MM420C TAM 1G 2-3/4" IN USE COVER

HUBBELL INCORPORATED DELAWARE

Catalog Number	MM420C
Manufacturer	HUBBELL INCORPORATED DELAWARE
Description	Weatherproof In-Use Cover, 1 Gang, 4.18 in (L) x 2.75 in (W) x 5.9 in (H), Horizontal Mount/Vertical Mount, Polycarbonate Material, Clear, 0.47 lb
Weight per unit	0.5310 (lbs/each)
Product Category	Boxes & Covers

Features

Cover Type	In-Use
Packaging Type	Shrinkwrap
Media	Yes
Pallet Quantity	768

Dimensions and Weight

Depth	3.05
Size	Standard
Width	4.5

Descriptions

Construction	Nonmetallic
Description	TAM 1G 2-3/4" IN USE COVER
Long Description	1-Gang Weatherproof In-Use Cover, EXTRA DUTY®, 16-in-1, 2-3/4 in. Deep, Clear
Product Type	1G WP Ext Dty 16IN1 Wiu CVR 2-3/4 DP CLR
	Weatherproof
Special Features	Extra Duty rated, 16-in1 configuration
Extra Long Description	RACO MM420C 1G WP EXT DTY 16IN1 WIU

Manufacturer Information

Brand	Taymac
	Raco-Taymac-Bell, a Hubbell affiliate
GTIN	00050169917275
UPC	565656
Series	EXTRA DUTY® Series

Taxonomies, Classifications, and Categories

Category Description	WEATHERPROOF BOXES & COVERS
Type	COVER

ELLIOTT ELECTRIC SUPPLY
We Deliver...Lower Cost, Quality Products, & Personal Service
805 South Timberlane Drive
El Dorado, AR 71730-0000
Phone: 8706396289
Fax: 8708648850

Packaging

Carton	1
Package	8
Standard Package	8
Weight Per Each	0.5310 (lbs/each)

Uses, Certifications, and Standards

Application	In Use
Standard	cULus Listed

SINGLE GANG WIU COVERS

Single Gang - While In use Covers - Extra Duty®
Horizontal/Vertical 16-in-1 **C04.1**





Catalog #: MM420C

APPLICATIONS

Designed for use whenever weatherproof protection is required while an outlet is in use.

PRODUCT FEATURES

High-impact polycarbonate construction provides maximum durability
Patented Quick-Fit™ keyhole mounting system allows installation in under a minute.
Includes attached gasket and mounting hardware
Pre-configured for GFCI with patented Knockout technology for alternate devices
Lockable tab

UL LISTED

File E116141

NEMA

3R Rated

NEC

2014 Compliant (article 406.9A & B) Extra Duty Rated

US PATENTS

7,348,486; 7,282,645; 7,119,277; 6,960,221; 6,790,816; 6,642,453

GENERAL PRODUCT INFORMATION

Color:	Clear

CONFIGURATION

Gangs:	1

PRODUCT MEASUREMENTS

Depth:	2-3/4 in.
Wt. Ea. (Lbs.):	0.531

PACKAGING

Package Type:	Shrink
Std. Pkg.:	8
Product UPC-A Labeled:	Yes
Weight (Lbs. Per/C):	53.10
Ship Carton Length (in.):	24.125
Ship Carton Width (in.):	4.688
Ship Carton Height (in.):	6.25
Ctn Weight (Lbs.):	4.25
Pallet Qty:	640.00
UPC Number:	050169917275
I2of5:	50050169917270