



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



MMX12AA9D6N00 Mmax 1P 230V In/3P 230V Out 9.6A 3.0HP FS3 W/O Emc *Eaton Corp*

Catalog Number	MMX12AA9D6N00
Manufacturer	Eaton Corp
Description	Eaton M-Max Series Sensorless Vector Adjustable Frequency Drive, Single-Phase In, Three-Phase Out, 9.6A, 3.0HP, 230V Input and Output Voltage, FS3, W/O Emc
Weight per unit	3.5 (lbs/each)
Product Category	Ac Drives

Features

dimensions	11.5000 IN X 5.5000 IN X 5.5000 IN
------------	------------------------------------

Descriptions

Description	MMAX 1P 230V IN/3P 230V OUT 9.6A 3.0HP FS3 W/O EMC
extra long description	ETN MMX12AA9D6N0-0 MMX 1P 230V 3P,9
Features	Demand more simplicity. The M-Max series of variable frequency drive is a compact system with a broad power range. Factor in the conformal board coating, unique mounting characteristics, simple programming, and its 50°C Rating and the M-Max is perfectly suited for machinery applications in many industries including material handling, HVAC, pumping and more.
Long Description	Eaton M-Max Series sensorless vector adjustable frequency drive, Single-phase in, three-phase out, 9.6A, 3.0HP, 230V input and output voltage, FS3, W/O EMC
Product Type	MMX 1P 230V 3P, 9.6A, 3.0HP, FS3, W/O Emc

Manufacturer Information

Brand	EATON CUTLER-HAMMER
GTIN	00786685268620
Manufacturers Part Number	MMX12AA9D6N0-0
UPC	786685268620

Taxonomies, Classifications, and Categories

Category Description	DRIVES
Type	Sensorless vector adjustable frequency drive

Availability

Status	Inactive
--------	----------



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Packaging

Carton	1
Weight Per each	3.5

Uses, Certifications, and Standards

Application	Elec Assemblies, Panels & OEM - Electrical Assemblies and EOEMs - Other
standard	CE Marked,C-Tick Compliant,RoHS Compliant