



**Southwire®**

**DRAW STUDS FOR MAX PUNCH® DRIVE UNITS**

● **EASY TO USE**  
Works with MP-01Pro



● **EASY TO USE**  
Works with MP-01



● **EASY TO USE**  
Works With MP360HP



**Southwire™**

TOOLS & EQUIPMENT

[ BUILT FOR DURABILITY.  
BUILT FOR RELIABILITY.  
BUILT FOR WORK. ]

**1-855-SWTOOLS**  
**(855-798-6657)**



Southwiretools.com



### Availability

#### MAX PUNCH® PRO DRAW STUDS

- 3/4" - Main Draw Stud - Stock #57717701 Model #PRDS34
- 7/16" - Medium Draw Stud - Stock #57717901 Model #PRDS716
- 1 1/8" - Large Draw Stud (for 2 1/2" – 4" Max Punch® and Max Punch® PRO Dies) - Stock #58306101 Model #PRDS118 (BLK/SI)

#### MAX PUNCH® DRAW STUDS

- 3/4" - Main Draw Stud - Stock #56825901 Model #MPDS12
- 7/16" - Medium Draw Stud - Stock #57717801 Model #MPDS716
- 3/8" - Small Draw Stud (for standard Max Punch® and Max Punch® Pro) - Stock #56826001 Model #MPDS38

#### MAX PUNCH® 360 DRAW STUDS

- 3/4" - Main Draw Stud - Stock #57578101 Model #HPDS34
- 7/16" - Small Draw Stud - Stock #57717601 Model #HPDS716

### Specifications

MODEL #	STOCK#	DESCRIPTION	LENGTH	WEIGHT	DIAMETR
PRDS34	57717701	3/4" Main Draw Stud - Max Punch® Pro	5"	8.7 oz	3/4"
PRDS716	57717901	7/16" Medium Draw Stud - Max Punch® Pro	4.25"	4.6 oz	7/16" - 3/4"
PRDS118	58306101	Large Draw Stud - 1 1/8" (for Mild Steel or Stainless Steel Large Dies)	4.4375"	15.6 oz	1 1/8"
MPDS38	56826001	3/8" Small Draw Stud - Max Punch®	3"	1.2 oz	3/8"
MPDS716	57717801	7/16" Medium Draw Stud - Max Punch®	3"	1.5 oz	7/16"
MPDS12	56825901	1/2" Main Draw Stud - Max Punch®	11.5"	4.4 oz	15/16"
HPDS716	57717601	7/16" Medium Draw Stud - Max Punch™ 360	4.25"	4.6 oz	7/16" - 3/4"
HPDS34	57578101	3/4" Main Draw Stud - Max Punch™ 360	5"	8.7 oz	3/4"

