



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



N6 #6 Cu Split Bolt *Nsi Industries*

| | |
|------------------|---|
| Catalog Number | N6 |
| Manufacturer | Nsi Industries |
| Description | Split Bolt Connector, #10 Awg (Range Of Equal Main and Tap-Solid) Conductor Size, #6 Awg (Range Of Equal Main and Tap-Stranded);#16 Awg (Minimum Tap With One Maximum Main-Stranded) Conductor Size, Non-Insulated, Copper;Copperweld Conductor Material, 2 Conductors, +90 °C Operating Temperature, 0.866 In Overall Length, Split Terminal, 600 V, 0.055 LB/Ea |
| Weight per unit | 0.0550 (lbs/each) |
| Product Category | Large Terminals & Connectors |

Features

| | |
|----------------------|----------------|
| Material | Copper |
| Number of Conductors | 2 |
| Poles | 1 |
| Voltage Rating | 600 V |
| Warranty | 1 YEAR |
| Wire Size | 10 SOL - 6 SOL |
| Wire Type | Class A & B |

Material, Color, and Finish

| | |
|--------|--------|
| Color | Copper |
| Finish | COPPER |

Dimensions and Weight

| | |
|------|-----------------|
| Size | L=.866 - W=.492 |
|------|-----------------|

Descriptions

| | |
|------------------------|--|
| Description | #6 CU SPLIT BOLT |
| extra long description | NSI N-6 Copper Split Bolt 500 |
| Features | Copper Split Bolt Connector 6 AWG Copper Split Bolt Connectors are high-strength solderless service connectors made of high-copper alloy for copper and copperweld wires. Type for two maximum wire sizes. |

Manufacturer Information

| | |
|------|----------------|
| GTIN | 00662381020024 |
| UPC | 662381020024 |

Taxonomies, Classifications, and Categories

| | |
|----------------------|--------------------|
| Category Description | SPLIT BOLTS |
| Type | Copper Split Bolts |



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Packaging

| | |
|-----------------|-------|
| Carton | 1 |
| Package | 100 |
| Weight Per each | 0.055 |

Uses, Certifications, and Standards

| | |
|--------------------------|------------------|
| Application | Wire Termination |
| environmental conditions | 90 C |
| standard | UL486B |
| Temperature Rating | 90 C |