



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



NPDB14201 PDB 1 Pole, Line 1X2/0-14, Load 4X4-14

Nsi Industries

Catalog Number	NPDB14201
Manufacturer	Nsi Industries
Description	100KA Short Circuit Current Rated Power Distribution Block. 1 X 2/0-14 Awg Line, 4 X 4-14 Awg Load Power Distribution Blocks Are Made Of Valox Nylon 6/6, Finger Safe Lexan 500R Polycarbonate Panels and Covers, High-Conductivity 6061-T6 Electro-Tin Plated Aluminum Alloy Connector. Each Block Can Stand Alone or Combine With Other Blocks to Form A Multi-Block Set, and Are Also Din Rail Mountable With Built In Locking Mechanism to Lock/Release.
Weight per unit	0.2760 (lbs/each)
Product Category	Power BLKS & Distribution BLKS

Features

amperage rating	175A
Material	6061-T6 Aluminum Body - Valox Nylon 6/6 Base - Lexan 500R Polycarbonate Panels and Covers
Number of Terminals	5
Voltage Rating	600
Warranty	1 YEAR
Wire Size	(1) 2/0-14 AWG(Line) - (4) 4-14 AWG(Load)

Material, Color, and Finish

Color	Black Base-Clear Panels and Covers
-------	------------------------------------

Dimensions and Weight

Size	L=3.560 - W=1.020 - H=2.570
------	-----------------------------



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Descriptions

Description	PDB 1 POLE, LINE 1X2/0-14, LOAD 4X4-14
extra long description	NSI NPDB-14-2/0-1 NPDB LINE 1X2/0-1
Features	100kA Short Circuit Current Rated Power Distribution Block. 1 x 2/0-14 AWG Line, 4 x 4-14 AWG Load Power Distribution Blocks are made of Valox Nylon 6/6, Finger Safe Lexan 500R Polycarbonate Panels and Covers, high-conductivity 6061-T6 Electro-Tin Plated aluminum alloy connector. Each block can stand alone or combine with other blocks to form a multi-block set, and are also Din Rail Mountable with built in locking mechanism to lock/release.
Long Description	100kA Short Circuit Current Rated Power Distribution Block. 1 x 2/0-14 AWG Line, 4 x 4-14 AWG Load Power Distribution Blocks are made of Valox Nylon 6/6, Finger Safe Lexan 500R Polycarbonate Panels and Covers, high-conductivity 6061-T6 Electro-Tin Plated aluminum alloy connector. Each block can stand alone or combine with other blocks to form a multi-block set, and are also Din Rail Mountable with built in locking mechanism to lock/release.
Product Type	NPDB Line 1X2/0-14 - Load 4X4-14
Special Features	100kA Short Circuit Current Rated (SCCR), Din Rail Mount with Locking Mechanism to lock/release block on Din Rail, Multi Pole Ganging, Finger Safe Lexan 500R Polycarbonate Panels & Covers.

Manufacturer Information

Brand	NSi
GTIN	00662381367501
Manufacturers Part Number	NPDB-14-2/0-1
UPC	662381367501

Taxonomies, Classifications, and Categories

Category Description	TERMINAL BLOCKS POWER DIST BLOCKS
Type	Single Primary (Line), Single Secondary (Load)

Packaging

Carton	1
Weight Per each	0.276

Uses, Certifications, and Standards

Application	NSI
Mounting standard	Slotted Holes in Base, 35mm DIN Rail w/Locking Feature UL1953 and UL1059 Listed, cULus