



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## NGH312033EC NGH 3 Pole 1200A LS 100% Rated BRKR English

Eaton Corp

Catalog Number	NGH312033EC
Manufacturer	Eaton Corp
Description	Eaton Series G Electronic Molded Case Circuit Breaker, NG-Frame, NG, Digitrip 310 RMS, Electronic LS Trip, Three-Pole, 1200A, 480 Vac, 100 Kaic At 240 Vac, 65 Kaic At 480 Vac, Line and Load, Imperial, 50/60 HZ, 100% Rated
Weight per unit	48.0 (lbs/each)
Product Category	20200113092527

### Features

Current Rating	1200 A
dimensions	6.0000 IN X 9.0000 IN X 9.0000 IN
frame	NG
media	Yes
Poles	Three-pole
Trip Type	Electronic LS
Voltage Rating	480 VAC

### Descriptions

Description	NGH 3 POLE 1200A LS 100% RATED BRKR ENGLISH
extra long description	ETN NGH312033EC NGH 3P 1200A LS 100
Features	The Eaton Series G Molded Case Circuit Breaker provides users with unparalleled performance and convenience. A patented contact design features high-speed "blow-open" action, resulting in superior circuit breaker performance. This globally-rated platform offers users high interruption ratings in a compact footprint with ease of in-field configuration applicable to a wide variety of industry and regional requirements. Choose from a selection of thermal magnetic and electronic trip units, available in curren
Long Description	Eaton Series G electronic molded case circuit breaker, NG-frame, NG, Digitrip 310 RMS, Electronic LS trip, Three-pole, 1200A, 480 Vac, 100 kAIC at 240 Vac, 65 kAIC at 480 Vac, Line and load, Imperial, 50/60 Hz, 100% rated
Product Type	NGH 3P 1200A LS 100% Rated BRK, English

### Manufacturer Information

Brand	Eaton
GTIN	00786685574356
Manufacturers Part Number	NGH312033EC
UPC	786685574356



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Taxonomies, Classifications, and Categories

Type	Electronic molded case circuit breaker
------	--

## Packaging

Carton	1
--------	---

Weight Per each	48
-----------------	----

## Uses, Certifications, and Standards

Application	Elec Assemblies, Panels & OEM - Electrical Assemblies, Panels and OEMs
-------------	--

Frequency Rating	50 to 60 Hz
------------------	-------------

standard	UL Listed, CSA Certified, HACR Rated
----------	--------------------------------------