ELLIOTT ELECTRIC SUPPLY
We Deliver...Lower Cost, Quality Products, & Personal Service
10917 Mill Creek Rd
Lenexa, KS 66219-0000
Phone: 9135637000
Fax: 9135637050

# P2400W 2G REWORK BOX

*ALLIED MOULDED*

| | |
|---|---|
| Catalog Number | P2400W |
| Manufacturer | ALLIED MOULDED |
| Description | Rework Box, Polycarbonate Material, Black, P-2400W Model, Non-Metallic Sheathed Cable Cable Entry, 4-1/8 in Width, Bracket Mount;Ear Wall Mount, 11 lb/EA |
| Weight per unit | 0.3330 (lbs/each) |
| Product Category | Bar Hangers & Outlet Box Accy. |

## Features

| | |
|---|---|
| Cable Entry | NON-METALLIC SHEATHED CABLE |
| Device Mounting Holes | 4 |
| Number Of Gangs | 2 |

## Dimensions and Weight

| | |
|---|---|
| Depth | 3-3/8 INCH |
| Height | 3-11/16 INCH |
| Width | 4-1/8 INCH |

## Descriptions

| | |
|---|---|
| Additional Information | Color Black; Application Old Work Residential Construction 2 Hour Fire Resistive Walls |
| Commodity Description | BAR HANGERS & OUTLET BOX ACCY |
| Description | 2G REWORK BOX |
| Long Description | 40 CI 2G DVC BOX EARS BRKTS KLMPS SWITCH BOX, GANGABLE, OLD WORK TYPE; POLYCARBONATE MATERIAL; 4-1/8 INCH; 3-11/16 INCH; 3-3/8 INCH; 2 GANG(S); UL, ANSI/UL 514C APPROVAL; METAL WING BRACKETS/NONMETAL EARS WALL COMPRESSION MOUNTING; 24 STANDARD PACKAGE; 40 CUBIC INCH CAPACITY |
| Product Type | Switch Box |
| Extra Long Description | GANGABLE TYPE; 4 7/64 INCH; 4 7/64 WIDTH IN INCH; 3 11/16 INCH; 3 11/16 HEIGHT IN INCH; 3 25/64 INCH; 3 25/64 DEPTH IN INCH; 2 GANG(S); UL APPROVAL; EARS, WING BRACKETS MOUNTING; 24 STANDARD PACKAGE; 40 CU INCH CAPACITY; FLEXBOX[R], SPEED KLAMPS[T] BRAND; P-240OW MODEL |

## Manufacturer Information

| | |
|---|---|
| Brand | Allied Moulded Products FLEXBOX[R] |
| GTIN | 00085339249122 |
| Manufacturers Part Number | P-240OW |
| Model | P-2400 |
| UPC | 881426 |

ELLIOTT ELECTRIC SUPPLY
We Deliver...Lower Cost, Quality Products, & Personal Service
10917 Mill Creek Rd
Lenexa, KS 66219-0000
Phone: 9135637000
Fax: 9135637050

## Taxonomies, Classifications, and Categories

| | |
|---|---|
| Category Description | SWITCH BOXES |
| Type | GANGABLE, OLD WORK |

## Packaging

| | |
|---|---|
| Carton | 1 |
| Package | 24 |
| Standard Package | 24 in |
| Weight Per Each | 0.3330 (lbs/each) |

## Uses, Certifications, and Standards

| | |
|---|---|
| Approval | UL, ANSI/UL 514C |
| Capacity | 40 Cubic Inch |
| Mounting | Metal Wing Brackets/Nonmetal Ears Wall Compression |