



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



NPDB14201 PDB 1 Pole, Line 1X2/0-14, Load 4X4-14

Nsi Industries

| | |
|------------------|--|
| Catalog Number | NPDB14201 |
| Manufacturer | Nsi Industries |
| Description | 100KA Short Circuit Current Rated Power Distribution Block. 1 X 2/0-14 Awg Line, 4 X 4-14 Awg Load Power Distribution Blocks Are Made Of Valox Nylon 6/6, Finger Safe Lexan 500R Polycarbonate Panels and Covers, High-Conductivity 6061-T6 Electro-Tin Plated Aluminum Alloy Connector. Each Block Can Stand Alone or Combine With Other Blocks to Form A Multi-Block Set, and Are Also Din Rail Mountable With Built In Locking Mechanism to Lock/Release. |
| Weight per unit | 0.2760 (lbs/each) |
| Product Category | Power BLKS & Distribution BLKS |

Features

| | |
|---------------------|---|
| amperage rating | 175A |
| Material | 6061-T6 Aluminum Body - Valox Nylon 6/6 Base - Lexan 500R Polycarbonate Panels and Covers |
| Number of Terminals | 5 |
| Voltage Rating | 600 |
| Warranty | 1 YEAR |
| Wire Size | (1) 2/0-14 AWG(Line) - (4) 4-14 AWG(Load) |

Material, Color, and Finish

| | |
|-------|------------------------------------|
| Color | Black Base-Clear Panels and Covers |
|-------|------------------------------------|

Dimensions and Weight

| | |
|------|-----------------------------|
| Size | L=3.560 - W=1.020 - H=2.570 |
|------|-----------------------------|



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Descriptions

| | |
|------------------------|--|
| Description | PDB 1 POLE, LINE 1X2/0-14, LOAD 4X4-14 |
| extra long description | NSI NPDB-14-2/0-1 NPDB LINE 1X2/0-1 |
| Features | 100kA Short Circuit Current Rated Power Distribution Block. 1 x 2/0-14 AWG Line, 4 x 4-14 AWG Load Power Distribution Blocks are made of Valox Nylon 6/6, Finger Safe Lexan 500R Polycarbonate Panels and Covers, high-conductivity 6061-T6 Electro-Tin Plated aluminum alloy connector. Each block can stand alone or combine with other blocks to form a multi-block set, and are also Din Rail Mountable with built in locking mechanism to lock/release. |
| Long Description | 100kA Short Circuit Current Rated Power Distribution Block. 1 x 2/0-14 AWG Line, 4 x 4-14 AWG Load Power Distribution Blocks are made of Valox Nylon 6/6, Finger Safe Lexan 500R Polycarbonate Panels and Covers, high-conductivity 6061-T6 Electro-Tin Plated aluminum alloy connector. Each block can stand alone or combine with other blocks to form a multi-block set, and are also Din Rail Mountable with built in locking mechanism to lock/release. |
| Product Type | NPDB Line 1X2/0-14 - Load 4X4-14 |
| Special Features | 100kA Short Circuit Current Rated (SCCR), Din Rail Mount with Locking Mechanism to lock/release block on Din Rail, Multi Pole Ganging, Finger Safe Lexan 500R Polycarbonate Panels & Covers. |

Manufacturer Information

| | |
|---------------------------|----------------|
| Brand | NSi |
| GTIN | 00662381367501 |
| Manufacturers Part Number | NPDB-14-2/0-1 |
| UPC | 662381367501 |

Taxonomies, Classifications, and Categories

| | |
|----------------------|--|
| Category Description | TERMINAL BLOCKS POWER DIST BLOCKS |
| Type | Single Primary (Line), Single Secondary (Load) |

Packaging

| | |
|-----------------|-------|
| Carton | 1 |
| Weight Per each | 0.276 |

Uses, Certifications, and Standards

| | |
|-------------------|---|
| Application | NSI |
| Mounting standard | Slotted Holes in Base, 35mm DIN Rail w/Locking Feature UL1953 and UL1059 Listed, cULus |