

Elliott Electric Supply

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr. 75964-0000, TX Nacogdoches Phone: 936-569-7941 Fax: 936-560-4685



Size

PD5NEWH Caseta 500W Elv Mult W/Neutral White

	DDENEMU
Catalog Number	PD5NEWH
Manufacturer	Lutron
Description	Lutron Caseta Wireless Elv+ Smart Dimmer Switch, With Phase Selectable Dimming For Led (250W), MLV (400W), Elv (500W), and Incandescent/Halogen (500W) Lighting, 120V, White
Weight per unit	0.2500 (lbs/each)
Product Category	Lighting Dimmers
Features	
actuator	Push-button
connection	Wire Leads
Connection Type	Wire Leads
insulation	Plastic
Material	Plastic/Metal
media	Yes
Poles	1
Switch Type	Push button
Voltage Rating	120
Wattage	500
Material, Color, and Finish	
Color	White
Finish	Gloss
Dimensions and Weight	

4.69 x 2.94;119 x 75



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr. 75964-0000, TX Nacogdoches Phone: 936-569-7941 Fax: 936-560-4685

	_						 •	
н	1	\sim	•	^	~		io	•
н		_	•					•
	_	·	.,	u		•	·	-

CASETA 500W ELV MULT W/NEUTRAL WHITE
LUT PD-5NE-WH Cas?ta ELV Dimmer 250
The Caseta ELV+ Smart Dimmer Switch with phase selectable dimming works with up to 250W of dimmable LED, 500W of incandescent/halogen/electronic low-voltage (ELV), or 400-Watt of magnetic low-voltage (MLV); Neutral wire connection and 10-Watt minimum load required for all load types. Out of the box, the dimmer is set to reverse phase for ELV/incandescent/halogen light loads. However, since it is phase selective, the dimmer output can be changed to forward phase for MLV lighting loads and other certain LED
Lutron Caseta Wireless ELV+ Smart Dimmer Switch, with Phase Selectable Dimming for LED (250W), MLV (400W), ELV (500W), and Incandescent/Halogen (500W) lighting, 120V, White
Cas?Ta Elv Dimmer 250W Led White
Controls 250 W LED (screw-base), 500 W incandescent/halogen, 400 VA (300 W) magnetic low-voltage, 500 W electronic low-voltage, 400 W Hi-lume 1 percent 2-wire LED driver, or 3.3 A Tu-Wire fluorescent ballast loads. Simple, intuitive design with on, off and raise/lower buttons. Provides true dimming from each location with Pico wireless remotes.

Mar

Brand	Lutron
GTIN	00784276217699
Manufacturers Part Number	PD-5NE-WH
UPC	784276217699

Taxonomies, Classifications, and Categories

Category Description	Residential dimmers, motion sensors, controls, & photo cells
Type	Wireless in-wall dimmer, multi-location/single-pole

Packaging

Carton	1
Weight Per each	0.25



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr. 75964-0000, TX Nacogdoches Phone: 936-569-7941 Fax: 936-560-4685

Uses, Certifications, and Standards

Application	Lighting Control
Enclosure	Plastic
environmental conditions	0 to 90% humidity, non-condensing. Indoor use only.
Frequency Rating	50 to 60
Mounting	WALLBOX
Operating Temperature	32 to 104
standard	UL, CUL, FCC, NOM, ICC, IFTEL