ELLIOTT ELECTRIC SUPPLY
We Deliver...Lower Cost, Quality Products, & Personal Service
926 Hwy 19
77320-0000, TX Huntsville
Phone: 936-439-0658
Fax: 936-439-9182



PD6WCLWH Caseta 150W Led Mult White

Lutron

Catalog Number	PD6WCLWH
Manufacturer	Lutron
Description	Dimmer, Button Switch, 120 V, 600 W, 50/60 HZ, Vacancy Sensor, Wall Mount, 2.6 In Length, 4.69 In Width, 2.94 In Height, White, +32 °F Operating Temperature, +104 °F Operating Temperature, 0.2 LB/Ea
Weight per unit	0.2000 (lbs/each)
Product Category	Lighting Dimmers

Features

actuator	Push-button
connection	Wire Leads
Connection Type	Wire Leads
insulation	Plastic
Material	Plastic/Metal
media	Yes
Poles	1
Voltage Rating	120
Wattage	600

Material, Color, and Finish

Finish	Gloss

Dimensions and Weight

Size	4.69 x 2.94;119 x 75

ELLIOTT ELECTRIC SUPPLY
We Deliver...Lower Cost, Quality Products, & Personal Service
926 Hwy 19
77320-0000, TX Huntsville
Phone: 936-439-0658
Fax: 936-439-9182

Descriptions

Description	CASETA 150W LED MULT WHITE
extra long description	LUT PD-6WCL-WH Cas?ta Smart Dimmer
Features	The Caseta Wireless Dimmer Switch works with up to 150 W of dimmable LED or 600W of incandescent/halogen. Existing hardwired 3-way switches will not work with this dimmer, for 3-way and multi-location applications Pico remotes must be used with this dimmer. Replace the existing switch with a Pico remote control and wall plate adapter to dim from every location (PICO-WBX-ADAPT sold separately). Use the Lutron Smart Hub (L-BDG2-WH) to connect the Caseta Smart Lighting Dimmer Switch to more leading smart home
Special Features	Controls 150 W LED/CFL (screw-base) or 600 W incandescent/halogen loads. Simple, intuitive design with on, off and raise/lower buttons. Provides true dimming from each location with Pico wireless remotes. Provides reliable dimming of dimmable LEDs/CFLs, as well as halogens and incandescents.

Manufacturer Information

GTIN	00784276071987
UPC	784276071987

Taxonomies, Classifications, and Categories

Category Description	Residential dimmers, motion sensors, controls, & photo cells
Type	Wireless in-wall dimmer, multi-location/single-pole

Packaging

Carton	1
Weight Per each	0.2

Uses, Certifications, and Standards

Application	Lighting Control
Enclosure	Plastic
Mounting	WALLBOX
Operating Temperature	32 to 104
standard	cUL, NOM, FCC, IFTEL, NEMA