

SMALL HOUSING - 22 WATT OPTIC FLOOD

REPLACES UP TO 100W MH



- Optical Grade Individual Acrylic Lenses
- More Footcandles Delivered to the Target
- Less Glare and Wasted Light



6.36"Wx9.36"Hx7.53"D
7 LBS

Design is Protected
by U.S. Patent
No. D710,530

ORDERING INFORMATION

CATALOG #	LUMENS	WATTAGE	LPW	CRI	CCT	DIMMING	VOLTS	REPLACES UP TO
PFS22LED	2,166	22 Watt LED	104	72	4500K	0-10V	120-277	100W MH
PFS22LED3K	1,978	22 Watt LED	93	73	3000K	0-10V	120-277	100W MH



OPTIONS

ADD SUFFIX #	DESCRIPTION	ADD SUFFIX #	DESCRIPTION
PC	120V Photocontrol	PM	208-277V Photocontrol

CATALOG #	DESCRIPTION
500-082BZ	Post-Top Fitter



ENERGY SAVINGS

LED		HID			
WATTAGE	ANNUAL COST	SOURCE WATTAGE	TOTAL WATTAGE USED	ANNUAL COST	ANNUAL SAVINGS
22	\$10	50	72	\$52	\$42
22	\$10	70	90	\$59	\$49
22	\$10	100	129	\$77	\$67

APPLICATIONS:



*The majority of Atlas Lighting Products are assembled in USA facilities by an American Workforce utilizing both Domestic and Foreign components

SMALL HOUSING - 22 WATT OPTIC FLOOD

REPLACES UP TO 100W MH



- Optical Grade Individual Acrylic Lenses
- More Footcandles Delivered to the Target
- Less Glare and Wasted Light



6.36"Wx9.36"Hx7.53"D
7 LBS

Design is Protected
by U.S. Patent
No. D710,530

ORDERING INFORMATION

CATALOG #	LUMENS	WATTAGE	LPW	CRI	CCT	DIMMING	VOLTS	REPLACES UP TO
PFS22LED	2,166	22 Watt LED	104	72	4500K	0-10V	120-277	100W MH
PFS22LED3K	1,978	22 Watt LED	93	73	3000K	0-10V	120-277	100W MH



OPTIONS

ADD SUFFIX #	DESCRIPTION	ADD SUFFIX #	DESCRIPTION
PC	120V Photocontrol	PM	208-277V Photocontrol

CATALOG #	DESCRIPTION
500-082BZ	Post-Top Fitter



APPLICATIONS:



ENERGY SAVINGS

LED		HID			
WATTAGE	ANNUAL COST	SOURCE WATTAGE	TOTAL WATTAGE USED	ANNUAL COST	ANNUAL SAVINGS
22	\$10	50	72	\$52	\$42
22	\$10	70	90	\$59	\$49
22	\$10	100	129	\$77	\$67



*The majority of Atlas Lighting Products are assembled in USA facilities by an American Workforce utilizing both Domestic and Foreign components