



## Mid-size combination wallplates

### Product description


2-Gang, 3-Gang




2-Gang toggle & duplex receptacle




2-Gang, toggle & decorator




2-Gang toggle & blank




2-Gang duplex receptacle & blank




2-Gang, duplex receptacle & decorator




3-Gang, 2 toggles & duplex receptacle




3-Gang, 2 toggles & decorator




1-Gang 1.406" hole



1-Gang 1.594" hole



1-Gang with 2.1563" hole



2-Gang with 2.1563" hole

### Combination 2-gang

Description	Material	Color suffix	Catalog no.	
Toggle & duplex receptacle	Polycarbonate	A, B, BK, GY, LA, RD, V, W	□ PJ18__	•
	Thermoset	A, B, LA, V, W	□ 2038__	• •
	302/304 Stainless steel	—	□ 93932	• •
Toggle & decorator	Polycarbonate	A, B, BK, GY, LA, V, W	□ PJ126__	•
	Thermoset	A, LA, V, W	□ 2053__	• •
	302/304 Stainless steel	—	□ 93937	• •
Toggle & blank	Polycarbonate	A, B, LA, V, W	□ PJ113__	•
Duplex receptacle & blank	Polycarbonate	A, B, BK, GY, LA, RD, V, W	□ PJ138__	•
Duplex receptacle & decorator	Polycarbonate	A, B, BK, GY, LA, RD, V, W	□ PJ826__	•

### Combination 3-gang

Description	Material	Color suffix	Catalog no.	
2 Toggles & duplex receptacle	Polycarbonate	A, B, BK, GY, LA, RD, V, W	□ PJ28__	•
2 Toggles & decorator	Polycarbonate	A, B, BK, GY, LA, V, W	□ PJ226__	•

## Mid-size power outlet wallplates

### Product description

1-Gang, 2-Gang

### Power outlet

Description	Material	Color suffix	Catalog no.	
1-Gang with 1.40" (35.7mm) hole	Polycarbonate	A, B, BK, GY, LA, RD, V, W	□ PJ7__	•
1-Gang with 1.59" (40.5mm) hole	Polycarbonate	B, GY, V, W	□ PJ720__	•
1-Gang with 2.15" (54.7mm) hole	Polycarbonate	B, BK, V, W	□ PJ724__	•
	Nylon	V	□ 5068__	• •
	Thermoset	A, B, V, W	□ 2068__	• •
2-Gang with 2.15" (54.7mm) hole	Polycarbonate	B, V, W	□ PJ703__	•

## Mid-size wallplate guide for power devices

### Wallplate for power devices

Power device catalog no.	Wallplate catalog no.
32B, 38B, 1233, 1234, 1253, 1254, 1257, 1258, 1263, 5700N, 5709N, 5716N, 5795N, 7985N	2068, 5068, PJ724, PJ703

### Color ordering information:

For ordering devices, include Catalog no. followed by the Color suffix: A (Almond), B (Brown), BK (Black), GY (Gray), LA (Light Almond), RD (Red), V (Ivory), W (White)

<b>A</b>	<b>B</b>	<b>BK</b>	<b>GY</b>	<b>LA</b>	<b>RD</b>	<b>V</b>	<b>W</b>	
(Almond)	(Brown)	(Black)	(Gray)	(Lt. Almond)	(Red)	(Ivory)	(White)	(Stainless Steel)

**Certification information:** 2000, 4000, 5000, ST & PJ series wallplates are cULus Listed; 93000 series wallplates are UL Listed and CSA Certified; 94000 series wallplates are UL Listed and CSA certified. **Specification information:** K-22

**Compliances, specifications and availability are subject to change without notice.**

Indicates NAFTA compliant - Page Q-32

RoHS compliant - Page Q-32