



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



PLED4022840VDIMC 40W 2X2 Led FLT PNL 40K

Keystone Technologies

Catalog Number	PLED4022840VDIMC
Manufacturer	Keystone Technologies
Description	Led Panel Light Fixture, 23.74 Inch Length X 23.74 Inch Width X 1.74 Inch Height Size; UI (Canada and Us), DLC Approval; Surface/Suspension Mount Mounting; Panel Light Fixture; Led Lamp Type; 40 Watt Lamp Wattage; 120 to 277 Volt Input Voltage
Weight per unit	7.5 (lbs/each)
Product Category	20170817162639

Features

area classification	Damp Location
Input Voltage	120 to 277 Volt
Intensity	4100 Lumen
Item	Panel Light Fixture
Lamp Type	LED
Lamp Wattage	40 Watt

Dimensions and Weight

Size	23.74 Inch Length x 23.74 Inch Width x 1.74 Inch Height
------	---------------------------------------------------------

Descriptions

Additional Information	RoHS Compliant; Driver Type 0 to 10 Volt Dimming; Nominal Size 2 Foot x 2 Foot; Color Temperature 4000 Kelvin; CRI 81.4; Efficacy 103 Lumen per Watt; Includes Adapter Sleeve; Temperature -4 to 104 Deg F
Commodity Description	LED SURFACE ARCHITECTURAL & SPECIFICATION LIGHTING
Description	40W 2X2 LED FLT PNL 40K
Long Description	LED PANEL LIGHT FIXTURE, 23.74 INCH LENGTH X 23.74 INCH WIDTH X 1.74 INCH HEIGHT SIZE; UL (CANADA AND US), DLC APPROVAL; SURFACE/SUSPENSION MOUNT MOUNTING; PANEL LIGHT FIXTURE; LED LAMP TYPE; 40 WATT LAMP WATTAGE; 120 TO 277 VOLT INPUT VOLTAGE

Manufacturer Information

Brand	Keystone Technologies
Manufacturers Part Number	KT-PLED40-22-840-VDIM
Model	800

Taxonomies, Classifications, and Categories

Category Description	LED ARCHITECTURAL & SPECIFICATION LIGHTING
----------------------	--------------------------------------------

Packaging

Carton	1
Weight Per each	7.5



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Uses, Certifications, and Standards

Approval	UL (Canada and US), DLC
Mounting	Surface/Suspension Mount