



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

1904 Dutton Drive
78666-0000, TX San Marcos
Phone: 512-392-4310
Fax: 512-392-4390



PLT4HTLO 14-1/2" 120LB BLK LCK CBL Tie *Panduit Corporation*

Catalog Number	PLT4HTLO
Manufacturer	Panduit Corporation
Description	Panduit PLT4H-TLO Locking Cable Ties Are Designed to Satisfy The Needs Of General Applications, While Delivering Consistent Performance and Reliability. Featuring A Curved Tip to Allow For Easy Pick Up From Flat Surfaces and Faster Initial Threading. Light-Heavy Cross Section, 14.5" (368MM) Length. For Indoor/Outdoor Use, Made Of Weather Resistant Nylon 6.6, Are Black In Color and Come In Packages Of 250.
Weight per unit	3.7 (lbs/each)
Product Category	Cable Ties & Wraps

Features

media	Yes
Tensile Strength	120

Dimensions and Weight

Length	14.5
Thickness	0.08

Descriptions

Description	14-1/2" 120LB BLK LCK CBL TIE
extra long description	PAN PLT4H-TLO Pan-Ty® PLT4H-TLO Cab
Long Description	Panduit PLT4H-TLO Locking Cable Ties are designed to satisfy the needs of general applications, while delivering consistent performance and reliability. Featuring a curved tip to allow for easy pick up from flat surfaces and faster initial threading. Light-heavy cross section, 14.5" (368mm) length. For Indoor/Outdoor use, made of Weather Resistant Nylon 6.6, are black in color and come in packages of 250.
Product Type	Pan-Ty® PLT4H-TLO Cable Tie, Black, Uv PA6.6, 14.5"L, 120LB,
Special Features	Indoor/Outdoor

Manufacturer Information

Brand	Panduit®
GTIN	00074983539420
Manufacturers Part Number	PLT4H-TLO
UPC	074983539420

Taxonomies, Classifications, and Categories

Type	Premium Cable Tie
------	-------------------



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

1904 Dutton Drive
78666-0000, TX San Marcos
Phone: 512-392-4310
Fax: 512-392-4390

Availability

minimum qty 250

Packaging

Carton 250

Package 500

Weight Per each 3.674

Uses, Certifications, and Standards

standard CSA Certified, RoHS Compliant