

Specifications



Photo is representative

Eaton PRL2A3600X42CL

Eaton Pow-R-Stock PRL2A panelboard, Interior, 480Y/277V, Three-phase, 4W, 600A, 42 circuit, Copper bus

General specifications

PRODUCT NAME	Eaton Pow-R-Stock PRL2A panelboard
CATALOG NUMBER	PRL2A3600X42CL
UPC	786687011125
PRODUCT LENGTH/DEPTH	85 in
PRODUCT HEIGHT	7 in
PRODUCT WIDTH	18 in
PRODUCT WEIGHT	75 lb
COMPLIANCES	NEMA Compliant
CERTIFICATIONS	UL 67



Product specifications

TYPE PRL2A Panelboard

Resources

AMPERAGE RATING	600A
BUS MATERIAL	Copper
BUS RATING	600 A
FEED TYPE	Top/bottom
NUMBER OF CIRCUITS	42
NUMBER OF POLES	Single-pole, three-pole
OPERATING TEMPERATURE	40°C
PHASE	Three-phase
SHORT-CIRCUIT RATING	35 A
WIRE SIZE	#4 AWG-350 kcmil
CIRCUIT BREAKER RATING	NEMA
CURRENT - MAX	600 A
NEMA RATING	NEMA 1, NEMA 3R
SERIES	PRL2a
VOLTAGE - MAX	480 V

MULTIMEDIA	Pow-R-Line Xpert family overview
SPECIFICATIONS AND DATASHEETS	Eaton Specification Sheet - PRL2A3600X42CL

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.

Follow us on social media to get the latest product and support information.



Specifications



Photo is representative

Eaton PRL2A3600X42CL

Eaton Pow-R-Stock PRL2A panelboard, Interior, 480Y/277V, Three-phase, 4W, 600A, 42 circuit, Copper bus

General specifications

PRODUCT NAME	Eaton Pow-R-Stock PRL2A panelboard
CATALOG NUMBER	PRL2A3600X42CL
UPC	786687011125
PRODUCT LENGTH/DEPTH	85 in
PRODUCT HEIGHT	7 in
PRODUCT WIDTH	18 in
PRODUCT WEIGHT	75 lb
COMPLIANCES	NEMA Compliant
CERTIFICATIONS	UL 67



Product specifications

TYPE PRL2A Panelboard

Resources

AMPERAGE RATING	600A
BUS MATERIAL	Copper
BUS RATING	600 A
FEED TYPE	Top/bottom
NUMBER OF CIRCUITS	42
NUMBER OF POLES	Single-pole, three-pole
OPERATING TEMPERATURE	40°C
PHASE	Three-phase
SHORT-CIRCUIT RATING	35 A
WIRE SIZE	#4 AWG-350 kcmil
CIRCUIT BREAKER RATING	NEMA
CURRENT - MAX	600 A
NEMA RATING	NEMA 1, NEMA 3R
SERIES	PRL2a
VOLTAGE - MAX	480 V

MULTIMEDIA	Pow-R-Line Xpert family overview
SPECIFICATIONS AND DATASHEETS	Eaton Specification Sheet - PRL2A3600X42CL

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.

Follow us on social media to get the latest product and support information.

