



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## PV1500LB58 1-1/2 PVC Coated Form 8

*Calpipe Industries, Inc*

Catalog Number	PV1500LB58
Manufacturer	Calpipe Industries, Inc
Description	Conduit Body, 0.002 Inch Urethane Coated Interior/0.04 Inch PVC Coated Exterior Steel Material; 10.67 Inch Length X 2.79 Inch Width X 4.07 Inch Height Size; Rigid Conduit Used On; 1-1/2 Inch Hub Size; LB Configuration; 2 Hub(S)
Weight per unit	N/A
Product Category	PVC Bodies & Boxes

### Features

Access Opening	BACK
Cover Type	PVC Coated Cast Iron, Screw-On
Form Type	FORM 8
Hub Location	90 Degree
Material	0.002 Inch Urethane Coated Interior/0.04 Inch PVC Coated Exterior Steel
Number of Hubs	2

### Dimensions and Weight

Hub Size	1-1/2 INCH
Size	10.67 Inch Length x 2.79 Inch Width x 4.07 Inch Height



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Descriptions

### Additional Information

Enclosure Type NEMA 4X; Constructional Feature Corrosion Resistant; Includes Cover, Plastic Encapsulated Stainless Steel Screw; Application Chemical and Petrochemical Plant, Water and Wastewater Treatment Facility, Pulp and Paper Mill, Cooling Tower, Mini

### Commodity Description

PVC CONDUIT BODIES,FS BX,JUNCT. BX

### Description

1-1/2 PVC COATED FORM 8

### extra long description

0.002 INCH URETHANE COATED INTERIOR/0.04 INCH PVC COATED EXTERIOR MATERIAL; 2.79 INCH WIDTH X 4.07 INCH HEIGHT SIZE; CONDUIT USED ON; 1-1/2 INCH HUB SIZE; LB CONFIGURATION; 2 HUB(S); UL 514B, CSA C22.2 APPROVAL; PVC COATED CAST IRON COVER TYPE; 90 DEGREE HUB LOCATION; FORM 8 FORM TYPE; BACK ACCESS OPENING; ENCLOSURE RATING NEMA 4X; INCLUDES PVC COATED CAST IRON COVER, PLASTIC ENCAPSULATED STAINLESS STEEL SCREW; PV MODEL

### Long Description

CONDUIT BODY, 0.002 INCH URETHANE COATED INTERIOR/0.04 INCH PVC COATED EXTERIOR STEEL MATERIAL; 10.67 INCH LENGTH X 2.79 INCH WIDTH X 4.07 INCH HEIGHT SIZE; RIGID CONDUIT USED ON; 1-1/2 INCH HUB SIZE; LB CONFIGURATION; 2 HUB(S)

### Product Type

Conduit Body

## Manufacturer Information

### Brand

Calpipe Industries, Inc

### GTIN

00847656074821

### Manufacturers Part Number

PV1500LB58

### UPC

847656074821

## Packaging

### Carton

1

### Weight Per each

0

## Uses, Certifications, and Standards

### Approval

UL 6/514B, CSA C22.2

### Configuration

LB

### Used On

RIGID CONDUIT