



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



PV1590EL00 1-1/2IN PVC Coated Rigid

Calpipe Industries, Inc

| | |
|------------------|--|
| Catalog Number | PV1590EL00 |
| Manufacturer | Calpipe Industries, Inc |
| Description | PVC Coated Steel Rigid Conduit Standard Radius Elbow, Standard Radius Type; Steel Material; 0.002 Inch Urethane Coated Interior, 0.04 Inch PVC Coated Exterior Finish; UI 6, Cul Approval; Ansi C80.1, Nema RN-1 Applicable Standard; 8 Standard Package |
| Weight per unit | 4.8 (lbs/each) |
| Product Category | Rigid Conduit Fittings - Steel |

Features

| | |
|---------------------|-----------------------|
| Applicable Standard | ANSI C80.1, NEMA RN-1 |
| Bend Angle | 90 Degree |
| Bend Radius | 8.25 INCH |
| End Type | THREADED |
| Material | Steel |

Material, Color, and Finish

| | |
|--------|--|
| Finish | 0.002 Inch Urethane Coated Interior, 0.04 Inch PVC Coated Exterior |
|--------|--|



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Descriptions

| | |
|------------------------|--|
| Additional Information | Length 10.6 Inch; Constructional Feature Corrosion Resistant; Application Petrochemical, Water and Wastewater Treatment Facility, Transportation and Infrastructure, Food, Dairy and Beverage, Mining, Marine and Coastal Facility, Chemical Plants, Steel Mill |
| Commodity Description | Rigid Conduit Fittings - Steel |
| Description | 1-1/2IN PVC COATED RIGID |
| extra long description | STANDARD RADIUS TYPE; STEEL MATERIAL; 0.002 INCH URETHANE COATED INTERIOR, 0.04 INCH PVC COATED EXTERIOR FINISH; UL 6, CUL APPROVAL; ANSI C80.1, NEMA RN-1 APPLICABLE STANDARD; 8 STANDARD PACKAGE; 1-1/2 INCH TRADE SIZE; THREADED END TYPE; 90 DEGREE BEND ANGLE; 8.25 INCH BEND RADIUS; LENGTH 10.6 INCH; CONSTRUCTIONAL FEATURE CORROSION RESISTANT; APPLICATION PETROCHEMICAL, WATER AND WASTEWATER TREATMENT FACILITY, TRANSPORTATION AND INFRASTRUCTURE, FOOD, DAIRY AND BEVERAGE, MINING, MARINE AND COASTAL FACILITY, |
| Long Description | PVC COATED STEEL RIGID CONDUIT STANDARD RADIUS ELBOW, STANDARD RADIUS TYPE; STEEL MATERIAL; 0.002 INCH URETHANE COATED INTERIOR, 0.04 INCH PVC COATED EXTERIOR FINISH; UL 6, CUL APPROVAL; ANSI C80.1, NEMA RN-1 APPLICABLE STANDARD; 8 STANDARD PACKAGE |
| Product Type | PVC Coated Steel Rigid Conduit Standard Radius Elbow |

Manufacturer Information

| | |
|---------------------------|-------------------------|
| Brand | Calpipe Industries, Inc |
| GTIN | 00847656053918 |
| Manufacturers Part Number | PV1590EL00 |
| Model | PV |
| UPC | 847656053918 |

Taxonomies, Classifications, and Categories

| | |
|----------------------|---|
| Category Description | COUPLINGS, ADAPTERS, REDUCERS, BUSHINGS, & CAPS |
| Type | STANDARD RADIUS |

Trade Size

| | |
|------------|------------|
| Trade Size | 1-1/2 INCH |
|------------|------------|

Packaging

| | |
|------------------|------|
| Carton | 1 |
| Standard Package | 8 W |
| Weight Per each | 4.81 |

Uses, Certifications, and Standards

| | |
|----------|-----------|
| Approval | UL 6, CUL |
|----------|-----------|