



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



PV1056RL Pan-Term® PV10-56R-L Ring *Panduit Corporation*

| | |
|------------------|--|
| Catalog Number | PV1056RL |
| Manufacturer | Panduit Corporation |
| Description | The PV10-56R-L Pan-Term® Terminal Is A Vinyl Insulated, Ring Terminal. Brazed Seam Protects Terminal Barrel From Splitting During The Crimp Process. Internal Barrel Serrations Assure Good Wire Contact and Maximum Tensile Strength. |
| Weight per unit | 0.2900 (lbs/each) |
| Product Category | Small Terminals & Connectors |

Features

| | |
|----------------|--------------|
| connection | Funnel Entry |
| insulation | Vinyl |
| Material | Copper |
| media | Yes |
| Voltage Rating | 600 |
| Wire Size | #10 |

Material, Color, and Finish

| | |
|--------|--------|
| Color | Yellow |
| Finish | Tinned |

Dimensions and Weight

| | |
|------|-------|
| Size | 5/16" |
|------|-------|

Descriptions

| | |
|------------------------|--|
| Description | PAN-TERM® PV10-56R-L RING |
| extra long description | PAN PV10-56R-L Pan-Term® PV10-56R-L |
| Long Description | The PV10-56R-L Pan-Term® Terminal is a vinyl insulated, ring terminal. Brazed seam protects terminal barrel from splitting during the crimp process. Internal barrel serrations assure good wire contact and maximum tensile strength. |
| Product Type | Pan-Term® PV10-56R-L Ring Terminal, Yellow, Vinyl, 10-12 Awg |

Manufacturer Information

| | |
|---------------------------|----------------|
| Brand | Panduit® |
| GTIN | 00074983801367 |
| Manufacturers Part Number | PV10-56R-L |
| UPC | 074983801367 |

Taxonomies, Classifications, and Categories

| | |
|----------------------|---------------|
| Category Description | TERMINALS |
| Type | Ring Terminal |



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Packaging

| | |
|-----------------|------|
| Carton | 50 |
| Package | 500 |
| Weight Per each | 0.29 |

Uses, Certifications, and Standards

| | |
|--------------------|---|
| Enclosure | Ring shape |
| Mounting | 5/16 |
| standard | cULus Listed 587H E52164, CSA Certified LR31212 |
| Temperature Rating | 221 Degrees Fahrenheit (105 Degrees Celsius) |