ELLIOTT ELECTRIC SUPPLY
We Deliver...Lower Cost, Quality Products, & Personal Service
17 Lou Stroup Drive
78801-0000, TX Uvalde
Phone: 830-278-1938
Fax: 830-278-1395



PV2000ST6 2IN PVC Coated Myers Hub

Calpipe Industries, Inc

Catalog Number	PV2000ST6
Manufacturer	Calpipe Industries, Inc
Description	Conduit Hub, Threaded Type; 0.002 Inch Urethane Coated Interior/0.04 Inch PVC Coated Exterior Steel Material; 4.25 Inch Diameter X 3.75 Inch Length Size; Conduit Used On; Ul 6/514B, Nec/Cec Approval; Non-Grounding; 2 Inch Trade Size; Corrosion Resistant
Weight per unit	N/A
Product Category	PVC Conduit Fittings & Accy

Features

Ground Type	Non-Grounding
Material	0.002 Inch Urethane Coated Interior/0.04 Inch PVC Coated Exterior Steel

Dimensions and Weight

Size	4.25 Inch Diameter x 3.75 Inch Length

ELLIOTT ELECTRIC SUPPLY
We Deliver...Lower Cost, Quality Products, & Personal Service
17 Lou Stroup Drive
78801-0000, TX Uvalde
Phone: 830-278-1938
Fax: 830-278-1395

Descriptions

Additional Information	Maximum Wall Thickness 0.125 Inch; Enclosure Type Class I Div 2, Class II Div 1 and 2, Class III Div 1 and 2, Class I Zone 1 AEx e II, Class I Zone 1 Ex e II, NEMA 2/3/3R/4/4X/11/12; Application Petrochemical, Water and Wastewater Treatment Facility, Tran
Commodity Description	PVC CONDUIT FITTINGS & ACCESSORIES
Description	2IN PVC COATED MYERS HUB
extra long description	THREADED TYPE; 0.002 INCH URETHANE COATED INTERIOR/0.04 INCH PVC COATED EXTERIOR STEEL MATERIAL; 4.25 INCH DIAMETER X 3.75 INCH LENGTH SIZE; CONDUIT USED ON; UL 6/514B, NEC/CEC APPROVAL; NON-GROUNDING; 2 INCH TRADE SIZE; CORROSION RESISTANT; MAXIMUM WALL THICKNESS 0.125 INCH; ENCLOSURE TYPE CLASS I DIV 2, CLASS II DIV 1 AND 2, CLASS III DIV 1 AND 2, CLASS I ZONE 1 AEX E II, CLASS I ZONE 1 EX E II, NEMA 2/3/3R/4/4X/11/12; APPLICATION PETROCHEMICAL, WATER AND WASTEWATER TREATMENT FACILITY, TRANSPORTATION AND
Long Description	CONDUIT HUB, THREADED TYPE; 0.002 INCH URETHANE COATED INTERIOR/0.04 INCH PVC COATED EXTERIOR STEEL MATERIAL; 4.25 INCH DIAMETER X 3.75 INCH LENGTH SIZE; CONDUIT USED ON; UL 6/514B, NEC/CEC APPROVAL; NON-GROUNDING; 2 INCH TRADE SIZE; CORROSION RESISTANT
Product Type	Conduit Hub

Manufacturer Information

Brand	Calpipe Industries, Inc
GTIN	00847656076214
Manufacturers Part Number	PV2000ST6
Model	ST
UPC	847656076214

Taxonomies, Classifications, and Categories

Type	THREADED

Trade Size

Trade Size	2 INCH

Packaging

Carton	1
Weight Per each	0

Uses, Certifications, and Standards

Approval	UL 6/514B, NEC/CEC
Used On	CONDUIT