

Eaton QBCAF1020

Catalog Number: QBCAF1020

Eaton QB AFCI circuit breaker, Type QBCAF 1-inch Circuit Interrupter, Single-pole, 120/240V, 10 kAIC, Combination AFCI, 20A



General specifications

Product Name	Catalog Number
Eaton QB AFCI circuit breaker	QBCAF1020
UPC	Product Length/Depth
786685244914	5.1 in
Product Height	Product Width
1.2 in	3.3 in
Product Weight	Certifications
0.2 lb	UL 489

Catalog Notes

HACR rated, for use in Sumter panels

Physical Attributes

Number of poles

Single-pole

Type

AFCI circuit breakers

Performance Ratings

Amperage Rating

20 A

Interrupt rating

10 kAIC

Resources

Brochures

[Loadcenters and Circuit Breakers](#)

Catalogs

[Eaton's Volume 4—Circuit Protection](#)

Specifications and datasheets

[Eaton Specification Sheet - QBCAF1020](#)

[Type QB \(1"\) Combination Arc Fault Circuit Interrupter](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)

Eaton QBCAF1020

Catalog Number: QBCAF1020

Eaton QB AFCI circuit breaker, Type QBCAF 1-inch Circuit Interrupter, Single-pole, 120/240V, 10 kAIC, Combination AFCI, 20A



General specifications

Product Name	Catalog Number
Eaton QB AFCI circuit breaker	QBCAF1020
UPC	Product Length/Depth
786685244914	5.1 in
Product Height	Product Width
1.2 in	3.3 in
Product Weight	Certifications
0.2 lb	UL 489

Catalog Notes

HACR rated, for use in Sumter panels

Physical Attributes

Number of poles

Single-pole

Type

AFCI circuit breakers

Performance Ratings

Amperage Rating

20 A

Interrupt rating

10 kAIC

Resources

Brochures

[Loadcenters and Circuit Breakers](#)

Catalogs

[Eaton's Volume 4—Circuit Protection](#)

Specifications and datasheets

[Eaton Specification Sheet - QBCAF1020](#)

[Type QB \(1"\) Combination Arc Fault Circuit Interrupter](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)