

Specifications



Photo is representative

Eaton QBGFT2050

Eaton QB GFCI circuit breaker, Ground fault circuit breaker, 50A, 10 kAIC, Two-pole, 120/240V, Common trip, 5 mA Trip sensitivity, #8-6 Cu, #6-4 Al, QBGF

General specifications

PRODUCT NAME	Eaton QB GFCI circuit breaker
CATALOG NUMBER	QBGFT2050
UPC	786676026697
PRODUCT LENGTH/DEPTH	6.5 in
PRODUCT HEIGHT	2 in
PRODUCT WIDTH	3.5 in
PRODUCT WEIGHT	0.8 lb
WARRANTY	1 year
CERTIFICATIONS	UL 489
CATALOG NOTES	HACR rated

Physical Attributes	
CIRCUIT BREAKER TYPE	QBGF
MOUNTING METHOD	Bolt-on
NUMBER OF POLES	Two-pole
TYPE	Ground fault circuit breaker
WIRE SIZE	#6-4 Al #8-6 Cu

Miscellaneous	
SPECIAL FEATURES	5 mA Trip Sensitivity

Performance Ratings	
AMPERAGE RATING	50 A
INTERRUPT RATING	10 kAIC
TRIP TYPE	Common trip
TRIP RATING	5 mA trip sensitivity
VOLTAGE RATING	120/240 V

Resources	
SPECIFICATIONS AND DATASHEETS	Eaton Specification Sheet - QBGFT2050

PROJECT NAME:
PROJECT NUMBER:
PREPARED BY:
DATE:



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2025 Eaton. All Rights Reserved.

Follow us on social media to get the latest product and support information.



Specifications



Photo is representative

Eaton QBGFT2050

Eaton QB GFCI circuit breaker, Ground fault circuit breaker, 50A, 10 kAIC, Two-pole, 120/240V, Common trip, 5 mA Trip sensitivity, #8-6 Cu, #6-4 Al, QBGF

General specifications

PRODUCT NAME	Eaton QB GFCI circuit breaker
CATALOG NUMBER	QBGFT2050
UPC	786676026697
PRODUCT LENGTH/DEPTH	6.5 in
PRODUCT HEIGHT	2 in
PRODUCT WIDTH	3.5 in
PRODUCT WEIGHT	0.8 lb
WARRANTY	1 year
CERTIFICATIONS	UL 489
CATALOG NOTES	HACR rated

Physical Attributes	
CIRCUIT BREAKER TYPE	QBGF
MOUNTING METHOD	Bolt-on
NUMBER OF POLES	Two-pole
TYPE	Ground fault circuit breaker
WIRE SIZE	#6-4 Al #8-6 Cu

Miscellaneous	
SPECIAL FEATURES	5 mA Trip Sensitivity

Performance Ratings	
AMPERAGE RATING	50 A
INTERRUPT RATING	10 kAIC
TRIP TYPE	Common trip
TRIP RATING	5 mA trip sensitivity
VOLTAGE RATING	120/240 V

Resources	
SPECIFICATIONS AND DATASHEETS	Eaton Specification Sheet - QBGFT2050

PROJECT NAME:
PROJECT NUMBER:
PREPARED BY:
DATE:



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2025 Eaton. All Rights Reserved.

Follow us on social media to get the latest product and support information.

