



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



QBHW2020 2 Pole 20A QBHW BRKR

Eaton Corp

Catalog Number	QBHW2020
Manufacturer	Eaton Corp
Description	Quicklag Industrial Thermal-Magnetic Circuit Breaker, 20A, QBHW Type, 22 Kaic, Two-Pole, Non-Interchangeable, 120/240V, Moisture-Fungus Treatment
Weight per unit	0.5500 (lbs/each)
Product Category	2 Pole Standard Trip Bolt-On

Features

dimensions	1.0000 IN X 1.0000 IN X 1.0000 IN
interrupt rating	22
Poles	2
Voltage Rating	120/240 V

Descriptions

Description	2 POLE 20A QBHW BRKR
extra long description	ETN QBHW2020F QBHW 2P 20A FUNGUS PR
Features	Eaton has a wide selection of UL rated miniature circuit breakers for loadcenters, fuseboxes, or similar devices. Each pole provides steel frame calibration and arc chutes with 5 - 100A continuous in one-, two-, and three-pole designs. A full-range of accessories expand customization options, including various mounting and ring tung termination options.
Long Description	Quicklag Industrial Thermal-Magnetic Circuit Breaker, 20A, QBHW type, 22 kAIC, Two-pole, Non-Interchangeable, 120/240V, Moisture-fungus treatment
Product Type	QBHW 2P 20A Fungus Proofed
Special Features	Moisture-fungus treatment

Manufacturer Information

Brand	Eaton
GTIN	00782113534541
Manufacturers Part Number	QBHW2020
UPC	782113534541

Taxonomies, Classifications, and Categories

Category Description	PANELBOARD BRANCH BREAKERS
Type	Thermal magnetic circuit breakers

Packaging

Carton	1
Package	12
Weight Per each	0.55



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Uses, Certifications, and Standards

Application

Generation - Renewable Energy - Alternative
EnergyOtherDatacenters - IT Space: CI and Hyper
ConvergedMarine Vessels and Equipment - Marine Vessels and
Equipment - OtherGeneration - Conventional Energy -
Conventional Energy

standard

CSA Certified,UL Listed