



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## QCR2060 QCR BKR 2P 60A 120/240vac Eaton Corp

Catalog Number	QCR2060
Manufacturer	Eaton Corp
Description	Eaton Quicklag Type QCR 1/2-Inch Industrial Thermal-Magnetic Circuit Breaker, Industrial Circuit Breaker, 60 A, 10 Kaic, Two-Pole, 120/240 V, Thermal-Magnetic, Cable-In/Cable-Out, QCR, Fixed
Weight per unit	0.2500 (lbs/each)
Product Category	2 Pole Din Rail Mount Circuit

### Features

connection	Cable-in/Cable-out
dimensions	4.6000 IN X 3.1000 IN X 1.2000 IN
interrupt rating	10
Poles	2
Voltage Rating	120/240 V

### Descriptions

Description	QCR BKR 2P 60A 120/240VAC
extra long description	ETN QCR2060 QCR BKR 2P 60A 120/240V
Features	Eaton has a wide selection of UL rated miniature circuit breakers for loadcenters, fuseboxes, or similar devices. Each pole provides steel frame calibration and arc chutes with 5 - 100A continuous in one-, two-, and three-pole designs. A full-range of accessories expand customization options, including various mounting and ring tung termination options.
Long Description	Eaton Quicklag Type QCR 1/2-inch Industrial Thermal-Magnetic Circuit Breaker, Industrial circuit breaker, 60 A, 10 kAIC, Two-pole, 120/240 V, Thermal-magnetic, Cable-in/cable-out, QCR, Fixed
Product Type	QCR BKR 2P 60A 120/240vac

### Manufacturer Information

Brand	Eaton
GTIN	00786679144466
Manufacturers Part Number	QCR2060
UPC	786679144466

### Taxonomies, Classifications, and Categories

Type	Thermal magnetic circuit breakers
------	-----------------------------------

### Packaging

Carton	1
Weight Per each	0.25



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Uses, Certifications, and Standards

Application

OtherGeneration - Renewable Energy - Alternative

EnergyGeneration - Conventional Energy - Conventional

EnergyDatacenters - IT Space: CI and Hyper ConvergedMarine

Vessels and Equipment - Marine Vessels and Equipment - Other

standard

UL Listed,CSA Certified,HACR Rated