

Eaton R5A3025U

Catalog Number: R5A3025U

Eaton rotary disconnect switch, 25 A, Non-fusible, Three-pole, Rotary switch, R5 Series, 600 V

General specifications

Product Name	Catalog Number
Eaton rotary disconnect switch	R5A3025U
UPC	Product Length/Depth
786685402864	2.57 in
Product Height	Product Width
3.35 in	1.77 in
Product Weight	Warranty
0.5 lb	Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.
Compliances	Certifications
CCC Marked	CSA Certified
	UL 508
	IEC Rated
	EN Listed
Catalog Notes	
Suitable as motor disconnect	



Physical Attributes

Number of poles

Three-pole

Series

R5

Performance Ratings

Amperage Rating

25A

Voltage rating

600 V

Miscellaneous

Product Category

Rotary Switch

Resources

Brochures

[Pringle Switches - Bolted contact switches](#)

Drawings

[R5A30_U 3D Model Xchange](#)

[R5A30_U 2D Drawing Xchange](#)

[R5A30_U 3D Inventor](#)

[R5A30_U 2D PDF](#)

[R5A30_U AutoCAD 2D Footprint](#)

[R5A30_U AutoCAD 2D Footprint \(mm\)](#)

Multimedia

[Switching Devices Flex Center](#)

Specifications and datasheets

[Eaton Specification Sheet - R5A3025U](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)

Eaton R5A3025U

Catalog Number: R5A3025U

Eaton rotary disconnect switch, 25 A, Non-fusible, Three-pole, Rotary switch, R5 Series, 600 V

General specifications

Product Name	Catalog Number
Eaton rotary disconnect switch	R5A3025U
UPC	Product Length/Depth
786685402864	2.57 in
Product Height	Product Width
3.35 in	1.77 in
Product Weight	Warranty
0.5 lb	Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.
Compliances	Certifications
CCC Marked	CSA Certified
	UL 508
	IEC Rated
	EN Listed
Catalog Notes	
Suitable as motor disconnect	



Physical Attributes

Number of poles

Three-pole

Series

R5

Performance Ratings

Amperage Rating

25A

Voltage rating

600 V

Miscellaneous

Product Category

Rotary Switch

Resources

Brochures

[Pringle Switches - Bolted contact switches](#)

Drawings

[R5A30_U 3D Model Xchange](#)

[R5A30_U 2D Drawing Xchange](#)

[R5A30_U 3D Inventor](#)

[R5A30_U 2D PDF](#)

[R5A30_U AutoCAD 2D Footprint](#)

[R5A30_U AutoCAD 2D Footprint \(mm\)](#)

Multimedia

[Switching Devices Flex Center](#)

Specifications and datasheets

[Eaton Specification Sheet - R5A3025U](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)