



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## RB12575 1-1/4" X 3/4" Reducing Bushing

*Appleton/Oz Gedney*

Catalog Number	RB12575
Manufacturer	Appleton/Oz Gedney
Description	Reducing Bushing, Size: 1-1/4 X 3/4 In, Material: Steel, Finish: Zinc Electroplate, Connection: NPT, Standard: Class I: Groups A, B, C, D, Class Ii: Groups E, F, G, Class Iii, UI 886 (1203), UI E10444, Csa C22.2 No. 25, C22.2 No. 30, Csa
Weight per unit	0.2300 (lbs/each)
Product Category	Rigid Conduit Fittings - Steel

### Features

connection	NPT
Material	Steel

### Material, Color, and Finish

Finish	Zinc Electroplate
--------	-------------------

### Dimensions and Weight

Size	1-1/4 X 3/4
------	-------------

### Descriptions

Description	1-1/4" X 3/4" REDUCING BUSHING
extra long description	APP RB125-75 RDC BUSH STL 1-1/4TO3/
Long Description	Reducing Bushing, Size: 1-1/4 X 3/4 IN, Material: Steel, Finish: Zinc Electroplate, Connection: NPT, Standard: Class I: Groups A, B, C, D, Class II: Groups E, F, G, Class III, UL 886 (1203), UL E10444, CSA C22.2 No. 25, C22.2 No. 30, CSA
Product Type	RDC Bush STL 1-1/4TO3/4 In NPT
Special Features	Smooth rounded integral bushing protects conductor insulation

### Manufacturer Information

Brand	Appleton
GTIN	00781381654654
Manufacturers Part Number	RB125-75
UPC	781381654654

### Taxonomies, Classifications, and Categories

Category Description	Locknuts, Bushings, Re-Bushings, Re-Washers, Threaded Plugs, Knockout Plugs
Type	Reducing Bushing

### Packaging

Carton	25
Package	100
Weight Per each	0.23



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Uses, Certifications, and Standards

Application

For Reducing Conduit Entries To A Smaller Size In Threaded Rigid  
And IMC Conduit Systems

standard

Class I: Groups A, B, C, D, Class II: Groups E, F, G, Class III, UL 886  
(1203), UL E10444, CSA C22.2 No. 25, C22.2 No. 30, CSA 065181